


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1552100180](#)
Status: **Active**
Overview: [Flamar Standard and Custom Cables for Industrial Automation](#)
Description: Flamar Control Cable, PVC Jacket, Unshielded, 5 Circuits, 1.00mm² with Green-Yellow Ground / 18 AWG with Green-Yellow Ground, 8.30mm (.327") Diameter, 1000.0m (3280.83') Length, Gray

Documents:
[Product Specification 1552100001-P1E \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

General	
Product Family	Cable
Series	155210
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	Flamar Standard and Custom Cables for Industrial Automation
Product Name	Flamar, Signal and Control
UPC	889056452281
Physical	
Bending Radius - Minimum	> 15xOD
Cable Length	1000.0m
Circuits (Loaded)	5
Color - Cable Jacket	Gray
Insulation	TPE
Material - Outer Jacket	PVC
Net Weight	0.010/g
Outer Jacket Diameter	8.30mm
Packaging Type	Reel
Temperature Range - Operating	+5° to +80°C
Wire Size AWG	18
Wire Size mm ²	1.00
Wire/Cable Type	UL AWM 2464 / CSA
Electrical	
Current - Maximum per Contact	Contact Molex
Voltage - Maximum	300V
Material Info	
Engineering Number	1X1000M
Reference - Drawing Numbers	
Product Specification	1552100001-P1E



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[155210](#) Series

Use With
DIN Valve Connectors [121201](#) , [121202](#) , [121207](#) , [121208](#) , [121205](#) , [121211](#)
Micro-Change (M12) [120071](#)
Ultra-Lock (M12) [120085](#)
GWconnect Heavy Duty Connectors [93601](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[155210-0180](#)