

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0877602618](#)
Status: **Active**
Overview: Milli-Grid Connector System
Description: 2.00mm Pitch Milli-Grid Header, Right-Angle, Through Hole, 26 Circuits, 2.54µm (100µ) Tin (Sn) Plating, Tray, Lead-Free

Documents:

3D Model	Application Specification 503940001-AS-000 (PDF)
Drawing (PDF)	Packaging Specification PK-89990-487-001 (PDF)
3D Model (PDF)	Test Summary 877610000-TS-000 (PDF)
Product Specification PS-87761-100-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification


CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	87760
Application	Board-to-Board, Signal, Wire-to-Board
Comments	Lead-Free version of 87049 series
Overview	Milli-Grid Connector System
Product Name	Milli-Grid
UPC	822350026352

Physical

Breakaway	No
Circuits (Loaded)	26
Circuits (maximum)	26
Color - Resin	Black
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Mated Height	4.00mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Nickel
Material - Resin	High Temperature Thermoplastic
Net Weight	1.003/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	2.60mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	2.540µm
Plating min - Termination	1.270µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	No



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[87760](#) Series

Mates With

Milli-Grid Vertical Through Hole Receptacle [79107](#) , [78787](#) . Milli-Grid Flex-to-Board Vertical Receptacle [79108](#) . Milli-Grid Vertical Surface Mount Receptacle [79109](#) , [78788](#) . Milli-Grid Top Entry Surface Mount Receptacle [87381](#) . Milli-Grid Side Entry Surface Mount Receptacle [87264](#)

Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-55° to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	2.0A
Voltage - Maximum	125V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	014
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	265
Material Info	
Reference - Drawing Numbers	
Application Specification	503940001-AS-000
Packaging Specification	PK-89990-487-001
Product Specification	PS-87761-100-001
Sales Drawing	SD-87760-109-001
Test Summary	877610000-TS-000

This document was generated on 09/17/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

87760-2618