

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0901200123

Status:

Active

Overview:

C-Grid III Interconnects

Description:

2.54mm Pitch C-Grid III Header, Single Row, Vertical, 3 Circuits, Tin (Sn) Plating

Documents:

Drawing (PDF)

3D Model

3D Model (PDF)

Product Specification PS-99020-0001-001 (PDF)

Application Specification 901190001-AS-000 (PDF)

Packaging Specification PK-90120-100-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		LR19980
UL		E29179
General		
Product Family		PCB Headers
Series		90120
Application		Signal, Wire-to-Board
Overview		C-Grid III Interconnects
Product Name		C-Grid III
UPC		800753747647
Physical		
Breakaway		Yes
Circuits (Loaded)		3
Circuits (maximum)		3
Color - Resin		Black
Durability (mating cycles max)		30
First Mate / Last Break		No
Flammability		94V-0
Glow-Wire Capable		No
Guide to Mating Part		No
Keying to Mating Part		None
Lock to Mating Part		None
Material - Metal		Brass
Material - Plating Mating		Tin
Material - Plating Termination		Tin
Material - Resin		Polyester
Net Weight		0.183/g
Number of Rows		1
Orientation		Vertical
PC Tail Length		2.90mm
PCB Locator		No
PCB Retention		None
PCB Thickness - Recommended		1.60mm
Packaging Type		Tray
Pitch - Mating Interface		2.54mm
Pitch - Termination Interface		2.54mm
Polarized to Mating Part		No
Polarized to PCB		No
Shrouded		No
Stackable		No
Surface Mount Compatible (SMC)		No
Temperature Range - Operating		-55° to +125°C
Termination Interface: Style		Through Hole



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

90120 Series

Mates With

90147 C-Grid PC Board Connector, 90123 C-Grid III Modular Crimp Housing

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	350V AC/DC

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	230

Material Info

Reference - Drawing Numbers

Application Specification	901190001-AS-000
Packaging Specification	PK-90120-100-001
Product Specification	PS-99020-0001-001
Sales Drawing	SD-90120-001-001

This document was generated on 01/05/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[90120-0123](#)