


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1708142008](#)
Status: **Active**
Overview: [NeoScale Mezzanine System](#)
Description: NeoScale High-Speed Mezzanine Receptacle, 2.80mm Pitch, 6x12, 72 Triads-100 Ohm (216 Circuits), 18.00mm Connector Height



Series image - Reference only

Documents:	
3D Model	Packaging Specification PK-170814-002-001 (PDF)
3D Model (PDF)	Test Summary TS-170807-2006-001 (PDF)
Drawing (PDF)	Datasheet (PDF)
Product Specification PS-170807-0001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Receptacles
Series	170814
Application	Board-to-Board, Signal
Overview	NeoScale Mezzanine System
Product Name	NeoScale
UPC	887191540771

Physical	
Circuits (Loaded)	216
Circuits (maximum)	216
Color - Resin	Black
Durability (mating cycles max)	100
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	No
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	21.033/g
Number of Rows	6
Orientation	Vertical
PCB Locator	Yes
PCB Retention	Yes
Packaging Type	Tray
Pitch - Mating Interface	2.80mm
Pitch - Termination Interface	2.80mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-55° to +85°C
Termination Interface: Style	Solder or Weld

Electrical	
Current - Maximum per Contact	1.0A
Grounding to PCB	No
Voltage - Maximum	30V AC (RMS)

Solder Process Data	
Duration at Max. Process Temperature (seconds)	020
Lead-freeProcess Capability	REFLOW

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[170814](#) Series

Mates With
NeoScale High-Speed Mezzanine Plug
[1708072008](#) , [1708072016](#) , [1708072020](#) , [1708072027](#)

Max. Cycles at Max. Process Temperature

001

Process Temperature max. C

260

Material Info

Reference - Drawing Numbers

Electrical Model Document

1708072126-000, EE-170807-2030-001,
EE-170807-2036-001, EE-170807-2100-001

Packaging Specification

PK-170814-002-001

Product Specification

PS-170807-0001-001

S-Parameter Model

SP-170807-2030-001, SP-170807-2036-001,
SP-170807-2100-001

Sales Drawing

SD-170814-2016-001

Test Summary

TS-170807-2006-001

This document was generated on 10/01/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[170814-2008](#) [170814-2016](#)