

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	<u>0932870001</u>
Status:	Active
Overview:	<u>SRC - Sealed Rectangular Connectors</u>
Description:	SRC Housing, Female, 84 Pin Signal (84 x MX150), SPS/Nylon, Black

Documents:

Drawing (PDF)	Packaging Specification 937320001-K (PDF)
Product Specification 850700010-K (PDF)	Test Summary STR-1389-001 (PDF)
Product Specification 850830010-P (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 937320001-P (PDF)	Product Literature (PDF)
Application Specification 850830010-A (PDF)	



Series image - Reference only

General

General	
Product Family	Crimp Housings
Series	<u>93287</u>
Application	Signal, Wire-to-Wire
More Detailed Tech Information	Current (max.) for 84 way fully loaded 6A with 30° temp rise (AWG 14 MX150)
Overview	<u>SRC - Sealed Rectangular Connectors</u>
Product Literature Order No	987650-7391
Product Name	SRC
UPC	884982405226

Physical

Circuits (maximum)	84
Circuits Detail	84 x MX150™
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	121.830/g
Number of Rows	14
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	0.30mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Material Info

Reference - Drawing Numbers

Application Specification	850830010-A
Packaging Specification	937320001-K
Product Specification	850700010-K, 850830010-P, 937320001-P
Sales Drawing	932870001-000
Test Summary	STR-1389-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

93287 Series

Mates With

SRC Signal Blade Housing 932880001 ,
937928400

Use With

MX150 Female Terminals 33012

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93287-0001](#)