

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1717223001](#)
Status: **Active**
Overview: [zQSFP+® Interconnect System](#)
Description: zQuad Small Form Factor Pluggable Plus (zQSFP+) Stacked Integrated 2-by-3 Connector and Cage with Metal EMI Gasket, 228 Circuit, Gold (Au) Over Nickel Plated, No Light Pipe

Documents:

Drawing (PDF)	Packaging Specification PK-171565-0001-001 (PDF)
3D Model	Test Summary TS-171565-0001-001 (PDF)
3D Model (PDF)	Symbol Footprint Data SYM-171722-3000-001 (PDF)
Product Specification PS-171565-0001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-171565-0002-001 (PDF)	Product Literature (PDF)

Agency Certification


UL E29179

General

Product Family I/O Connectors
Series [171722](#)
Application Board-to-Board, Module-to-Board, Wire-to-Board
Component Type Receptacle
Electrical Model Yes
Overview [zQSFP+® Interconnect System](#)
Product Name zQSFP Plus, zQSFP+
Type N/A
UPC 887191261812

Physical

Circuits (Loaded) 228
Circuits (maximum) 228
Color - Resin Black
Durability (mating cycles max) 100
Flammability 94V-0
Keying to Mating Part None
Lock to Mating Part Yes
Material - Metal Copper Alloy
Material - Plating Mating Gold
Material - Plating Termination Matte Tin
Material - Resin High Temperature Thermoplastic
Net Weight 90.848/g
Number of Rows 2
Orientation Right Angle
PC Tail Length 1.20mm
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.57mm
Packaging Type Tray
Panel Mount N/A
Pitch - Mating Interface 0.80mm
Plating min - Mating 0.762µm
Plating min - Termination 0.762µm
Polarized to Mating Part Yes
Polarized to PCB Yes
Ports 6
Surface Mount Compatible (SMC) No
Temperature Range - Operating -40° to +85°C



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[171722 Series](#)

Mates With

QSFP Cable Assembly [74757](#)

Termination Interface: Style	Through Hole - Compliant Pin
Electrical	
Current - Maximum per Contact	0.5A
Grounding to Panel	Yes
Shield Type	EMI Fingers
Voltage - Maximum	30V AC (RMS)/DC
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-171565-0002-001
Electrical Model Document	EE-171081-3000-001
Packaging Specification	PK-171565-0001-001
Product Specification	PS-171565-0001-001
S-Parameter Model	SP-171081-3000-001
Sales Drawing	SD-171722-2000-001
Symbol/Footprint Data	SYM-171722-3000-001
Test Summary	TS-171565-0001-001

This document was generated on 08/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

171722-3001