

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1060253150

Status:

Active

Overview:

Optical Connectivity Solutions

Description:

LC Duplex Connector, Singlemode, 127µm Ceramic Ferrule, 3.00mm Duplex Cable, Beige Housing, Straight, Two Piece Clip



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

General	
Product Family	Fiber Optic Connectors
Series	106025
Cable Size	3.00mm
Material - Housing	PEI
Mode	Singlemode
Overview	Optical Connectivity Solutions
Product Name	LC
UPC	822350260237
Wire/Cable Type	Duplex
Physical	
Alignment Sleeve	Ceramic
Angled Physical Contact (APC)	No
Boot Color	Beige
Boot Type	Straight
Color - Resin	Beige
Ferrule Hole Size	127µm
Ferrule Material	Ceramic
Gender	Plug
Mounting Style	Adhesive
Net Weight	2.944/g
Ports	2
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	860253150
Reference - Drawing Numbers	
Sales Drawing	SD-106025-X1X0-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
1,2-
Benzenedicarboxylic
acid, dihexyl ester,
bra
Terphenyl,
hydrogenated
Dibutylbis(pentane-2,4-
dionato-O,O')tin
2-ethylhexyl 10-
ethyl-4,4-dioctyl-7-
oxo-8-oxa-3,
Disodium-octaborate
Ammonium-
pentadecafluorooctanoate
1,3-Propanesultone
Dibutyltin-dichloride
1,2-diethoxyethane
Disodium 3,3'-[[1,1'-
Biphenyl]-4,4'-
Diylbis(Azo)
Octamethylcyclotetrasiloxane
Decamethylcyclopentasiloxane
Dodecamethylcyclohexasiloxane
Benzo(ghi)perylene
diisohexyl phthalate
Perfluorohexane-1-
sulphonic acid and its
salts
Methylhexahydrophthalic
anhydride
Perfluorononan-1-
oic acid
(2,2,3,3,4,4,5,5,6,6,7
Diocetyl tin dilaurate,
stannane, dioctyl-,
bis(co

China RoHS

Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o
Pyrene
Tris(4-nonylphenyl,
branched and linear)
phosphi
Nonadecafluorodecanoic
acid (PFDA) and its
sodium
Zirconia
Aluminosilicate
Refractory Ceramic
Fibr
Hexabromocyclododecane
(HBCDD)
Boric acid
n-pentyl-
isopentylphthalate
1,2-
Benzenedicarboxylic
acid, dipentyl ester, br
diisohexyl phthalate
Benzo(ghi)perylene
Lead oxide sulfate
(Pb2O(SO4))
Lead-dinitrate
pyrochlore, antimony
lead yellow
Cadmium
Lead
Cadmium-oxide
Diboron-trioxide
Decabromodiphenylether
1,2-bis(2-
methoxyethoxy)ethane
1,2-
Benzenedicarboxylic
acid, bis(2-
methoxyethyl
Boric acid, disodium
salt, hydrate
Lead sulfochromate
yellow
Lead chromate
molybdate sulfate red
Lead-titanium-trioxide
bis(2-(2-
methoxyethoxy)ethyl)
ether
Dipentyl phthalate
Phenanthrene
Dihexyl-phthalate
Dicyclohexyl-
phthalate
Fatty Acids, C16-18,
Lead Salts
[Phthalato(2-)]dioxotrilead
Silicic acid (H2Si2O5),
barium salt (1:1),
lead-
Sulfurous Acid, Lead
Salt, Dibasic
Cadmium Hydroxide
Cyanamide, lead(2+)
salt (1:1)

Lead titanium
zirconium oxide
Tetralead-trioxide-
sulphate
Lead-titanium-trioxide
Halogen-Free
Status
Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[106025](#) Series

Mates With

[106115](#) LC Duplex EMI Adapter. [106123](#) LC Quad Adapter. LC Duplex Adapter [106125](#) , [106126](#) , [106127](#) , [106128](#)

This document was generated on 08/26/2021

PLEASE CHECK [WWW.MOLEX.COM](#) FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

106025-3150