

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1120955158

Status:


Active

Overview:

IP67-Rated HarshIO Modules

Description:

Brad HarshIO Digital Module for PROFINET, Classic 60mm, IP67, 8 ports M12, 4 Motors + 8 User conf. Inputs/Outputs, PNP, M12 5-Pole Power



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

General	
Product Family	Industrial I/O Modules
Series	112095
Application	Material Handling Systems
Approvals	PI, UL, cUL, CE
Comments	4 Motorized Drive Rollers and 8 user configurable input / output channels., 4 Motorized Drive Rollers and 8 user configurable input / output channels.
EPLAN	Yes
IP Rating	IP67
Overview	IP67-Rated HarshIO Modules
Product Name	HarshIO PROFINET IO
Protocol	PROFINET
Software Downloads	TCDEP-8YMP-D1U-G
UPC	191128315296
Physical	
Bus Input	4-pole Micro-Change (M12), D-Coded, Female
Bus Output	4-pole Micro-Change (M12), D-Coded, Female
Format	Classic (60mm)
Housing Width	60.00mm
I/O Connector	5-pole Ultra-Lock (M12), A-Coded, Female
I/O Ports	8x M12
I/O Signal Mix	4 motors, 8 input / output configurable
Mechanical Shock	10G, 11ms, 3 AXIS
Net Weight	597.000/g
Power Input	5-pole Mini-Change, Male
Power Output	None
Temperature Range - Operating	-30°C to +40°C
Vibration	MIL-STD-202F, Test Method 204D,Condition A
Electrical	
Current - Maximum Output	2.0A per Channel
EMC	IEC 61000-6-2
Input Delay	1 ms
Input Device Supply	200 mA per port at 20°C
Input Type	PNP or Dry Contact
Material Info	
Engineering Number	TCDEP-8YMP-D1U-G
Reference - Drawing Numbers	
Sales Drawing	1120725507-000

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

112095 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1120955158](#)