

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1121035000](#)
Status: **Active**
Overview: [IP67-Rated HarshIO Modules](#)
Description: Brad IO-Link Digital Hub, IP67, 8 Ports M12, 16 Inputs, PNP



Documents:	
3D Model	RoHS Certificate of Compliance (PDF)
Drawing (PDF)	Product Literature (PDF)
3D Model (PDF)	

General	
Product Family	Industrial I/O Modules
Series	112103
Application	Filling and Packaging Machines, Machine Tool Industry, Material Handling Systems
Approvals	CE, UL, cUL
IP Rating	IP67
Overview	IP67-Rated HarshIO Modules
Product Name	IO-Link Digital Hub
Protocol	IO-Link
Software Downloads	TEDIO-8xxP-808
UPC	889056236461
Physical	
Bus Input	4-pole Ultra-Lock (M12), A-Coded, Male
Bus Output	N/A
Format	Classic (54mm)
Housing Width	54.00mm
I/O Connector	5-pole M12, A-Coded, Female
I/O Ports	8x M12
I/O Signal Mix	16 input
Mechanical Shock	EN 60068-2-6, EN 60068-2-29
Power Input	None
Power Output	None
Temperature Range - Operating	-25°C to +70°C
Vibration	EN 60068-2-29, EN 60068-2-6
Electrical	
Current - Maximum Output	0.5A per Channel
EMC	EN 61000-6-2, EN 61000-6-4
Input Delay	0,1,3 or 5 ms
Input Device Supply	100 mA per port at 25°C
Input Type	PNP or Dry Contact
Material Info	
Engineering Number	TEDIO-8D0P-808
Reference - Drawing Numbers	
Sales Drawing	1121035000-000

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[112103](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[112103-5000](#)