

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1726732006](#)
Status: **Active**
Overview: [Super Sabre Connector System](#)
Description: 7.50mm Pitch Super Sabre Plug Crimp Housing, UL 94V-0, 6 Circuits

Documents:
[Drawing \(PDF\)](#) [Packaging Specification PK-43680-001-001 \(PDF\)](#)
[3D Model](#) [Test Summary TS-171825-001-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-171825-001-001 \(PDF\)](#)

Agency Certification
CSA LR19980
UL E29179

General
Product Family Crimp Housings
Series [172673](#)
Application Power, Wire-to-Board, Wire-to-Wire
Overview [Super Sabre Connector System](#)
Product Name Super Sabre
UPC 889056026000

Physical
Circuits (maximum) 6
Color - Resin Black
Flammability 94V-0
Gender Plug
Glow-Wire Capable No
Keying to Mating Part Yes
Lock to Mating Part Yes
Material - Resin Nylon
Net Weight 8.851/g
Number of Rows 1
Packaging Type Carton
Panel Mount No
Pitch - Mating Interface 7.50mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40° to +125°C

Electrical
Current - Maximum per Contact 34.0A

Solder Process Data
Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers
Packaging Specification PK-43680-001-001
Product Specification PS-171825-001-001
Sales Drawing SD-172673-001-001
Test Summary TS-171825-001-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2021)4569-DC (8
July 2021)
Halogen-Free
Status
Low-Halogen
For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[172673](#) Series

Mates With
[172672](#) Super Sabre Receptacle Crimp
Housing

Use With
[171826](#) Super Sabre Male Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[172673-2006](#)