

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200878805

Status:

Active

Overview:

Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable

Description:

Micro-Change (M12) to Nano-Change (M8) Double-Ended Cordset with Knurled Hexnut, 3 Poles, Female (Straight) to Male (Straight), 24 AWG, WSOR Cable, 0.60m (1.97') Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Cordsets
Series	120087
Connector End A	Micro-Change (M12)
Connector End B	Nano-Change (M8)
IP Rating	IP67
Material - Contact	Brass
Overview	Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable
Product Name	Micro-Change (M12), Nano-Change (M8)
Protocol	N/A
Region	Europe
Type	Double Ended
UPC	889056132701
Physical	
Cable Diameter	4.50mm (.177")
Cable Length	0.60m (1.97')
Color - Cable Jacket	Black
Coupling Style	Knurled Hexnut, Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	36.740/g
Orientation	Straight to Straight
Poles	3
Temperature Range - Operating	-25°C to +85°C
Wire Size AWG	24
Wire/Cable Type	WSOR
Electrical	
Current - Maximum per Contact	3.0A, 4.0A
Voltage - Maximum	60V
Material Info	
Engineering Number	483030B41M006
Reference - Drawing Numbers	
Sales Drawing	1200878806-000, SD-120087-058

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

China RoHS

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

120087 Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1200878805