

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2010212012](#)
Status: **Active**
Overview: [Slim-Grid Board-to-Board Connectors](#)
Description: Slim-Grid Header, 12 Circuits, Through Hole, Right-Angle, Shrouded, 0.05µm Gold (Au) Plated, 4.00mm Tail Length, without Peg, Tube, Lead-Free

Documents:

Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 2009890001-000 (PDF)	Product Literature (PDF)
Packaging Specification 2010210001-000 (PDF)	

General


Product Family	PCB Headers
Series	201021
Application	Board-to-Board, Signal
Comments	4.3 Amps per Pole with only 1 contact powered up 1.4 Amps per Pole with max contacts powered up
Overview	Slim-Grid Board-to-Board Connectors
Product Name	Slim-Grid
UPC	889056921053

Physical

Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Black
Durability (mating cycles max)	500
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	0.509/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	4.00mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	3.00mm
Packaging Type	Tube
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.051µm
Plating min - Termination	2.000µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Temperature Range - Operating	-55° to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	1.4A
-------------------------------	------



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[201021](#) Series

Mates With

Slim-Grid Receptacle [78120](#)

Voltage - Maximum	125V AC
Solder Process Data	
Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Packaging Specification	2010210001-000
Product Specification	2009890001-000
Sales Drawing	2010210024-000

This document was generated on 09/02/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[201021-2012](#)