

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300920049](#)
Status: **Active**
Overview: [Slip Rings](#)
Description: Aero-Motive Enclosed Slip Ring, 30A, 10 AWG, 4 Conductors

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR19099
UL	E110371
General	
Product Family	Slip Rings
Series	130092
Center Bore Diameter	N/A
Component Type	Enclosed
Current - Maximum per Contact	30.0A
Mounting Style	Vertical
Number of Conductors	4
Overview	Slip Rings
Packaging Type	Carton
Product Name	Aero-Motive
Speed (RPM)	Continuous 10
Temperature Range - Operating	-40°C to +120°C
UPC	78678867705
Voltage - Maximum	600V
Wire Size AWG	10
Material Info	
Engineering Number	ISRC34



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130092](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300920049