

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2016060630

Status:

Active

Overview:

High-Current, Universal-Clamp Terminal Blocks

Description:

High Current Universal Clamp Terminal Block, 35.00mm DIN-rail or Screw Mount, 285.0A / 600V, Grey Housing and Cover, 1 Circuit



Series image - Reference only

Documents:	
3D Model	RoHS Certificate of Compliance (PDF)
3D Model (PDF)	Product Literature (PDF)
Drawing (PDF)	

Agency Certification	
UL	E48521
General	
Product Family	Terminal Blocks
Series	201606
Application	Wire-to-Wire
Component Type	One Piece
Overview	High-Current, Universal-Clamp Terminal Blocks
Product Name	Universal Clamp
Type	Universal Clamp
UPC	78172551130
Physical	
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Grey
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Aluminum
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyamide
Number of Rows	1
Orientation	Vertical
Panel Mount	Screws
Pitch - Mating Interface	N/A
Polarized to Mating Part	N/A
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Screw
Wire Size AWG	1/0+1/0, 2+2, 2+2+2, 300 MCM-2
Wire Size mm²	33.60+33.60, 33.60+33.60+33.60, 33.60-152.01, 53.00+53.00
Electrical	
Current - Maximum per Contact	285.0A
Voltage - Maximum	600V
Material Info	
Engineering Number	MX-KE63
Reference - Drawing Numbers	
Sales Drawing	2016060630-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

201606 Series

This document was generated on 09/06/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[201606-0630](#)