








4 CIRCUIT SHOWN



- NOTES:
- 1. MATERIAL: SEE TABLE
 - 2. FINISH: SEE TABLE
 - 3. INCH DIMS ARE SHOWN IN BRACKETS [XXX].
 - 4. "XX" REFERS TO THE NUMBER OF CIRCUITS.
 - 5. ALL COMPONENTS ARE ROHS COMPLIANT.

TOLERANCES			
MM	TOL	INCH	TOL
0-6	±0.25	0-.24	±.010
>6-30	±0.40	.24-1.18	±.016
>30-120	±0.50	1.18-4.76	±.020
>120	±0.80	>4.76	±.031

5	XX	SCREW&WASHER, #6-32X.250, PAN, PH/SL (-50 OPT)	STEEL	ZN, CLEAR CHROMATE
4	XX	SCREW, #6-32X.250, BHD, PH/SL (-49 OPT)	BRASS	NICKEL PLATE
3	XX	SCREW, #6-32X.250, BHD, PH/SL (STD)	STEEL	ZN, CLEAR CHROMATE
2	XX	TERMINAL, PC, #6-32	BRASS	TIN PLATE
1	1	INSULATOR, SR, NO MTG.	30% G.F. PBT	BLACK
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

DOCUMENT STATUS	P1	RELEASE DATE	2019/12/02	17:26:01
-----------------	----	--------------	------------	----------

SYMBOLS

≡ = 0

≡ = 0

≡ = 0

≡ = 0

≡ = 0

≡ = 0

≡ = 0

≡ = 0

≡ = 0

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

SCALE

2:1

GENERAL TOLERANCES (UNLESS SPECIFIED)

MM

INCH

4 PLACES ± --- ± ---

3 PLACES ± --- ± SEE CHART

2 PLACES ± SEE CHART ± SEE CHART

1 PLACE ± SEE CHART ± ---

0 PLACES ± --- ± ---

ANGULAR TOL ± ---

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC: ADDED TOLERANCE TABLE

EC NO: 626833

DRWN: ABENJAMINLW 2019/11/05

CHK'D: DACHAMMER 2019/11/05

APPR: JFMURPHY 2019/12/02

INITIAL REVISION:

DRWN: CYORK 2006/07/12

APPR: RDEROSS 2006/07/13

THIRD ANGLE PROJECTION

DRAWING

SERIES

B-SIZE 38710

molex

9.53MM [.375"] SR BTS ASSY, PC TERM. WITHOUT MTG. ENDS, LOW PROF.

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER

DOC TYPE

DOC PART

REVISION

SD-38710-005

PSD 001 B

MATERIAL NUMBER

CUSTOMER

SHEET NUMBER

SEE SHEET-2

GENERAL MARKET

1 OF 2

10

9

8

7

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[38710-6904](#) [38710-6914](#) [38710-6912](#) [38710-6911](#) [38710-6313](#) [38710-6902](#) [38710-6907](#) [38710-6315](#) [38710-6316](#) [38710-6318](#) [38710-6319](#) [38710-6321](#) [38710-6322](#) [38710-6323](#) [38710-6324](#) [38710-6325](#) [38710-6326](#) [38710-6903](#) [38710-6906](#) [38710-6909](#) [38710-6916](#) [38710-6918](#) [38710-6925](#) [38710-7515](#) [38710-7516](#) [38710-7517](#) [38710-7519](#) [38710-7520](#) [38710-7525](#)