





REF. -50 OPT. SCREW
(WHERE APPLICABLE)



3 CIRCUIT SHOWN



NOTES:

1. MATERIAL: SEE TABLE
2. FINISH: SEE TABLE
3. "XX" REFERS TO THE QUANTITY OF CIRCUITS.
4. ALL COMPONENTS ARE ROHS COMPLIANT.

				ADD P/N 387291662		EC NO: IFG2015-0005		DRAWN BY DRWINRSTONE 2014/07/01		CHKD BY ARDEN 2014/07/03		APPR: JFMURPHY 2014/07/29		REV		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
																▽=0		mm INCH		DRAWN BY DATE		TITLE					
6 XX SCREW&WASHER, #6-32X.250 PAN, PH/SL (-50 OPT)				STEEL		ZN, CLEAR CHROMATE										4 PLACES ± --- ± ---		± --- INCH		C. YORK 2006/08/18		9.53MM [.375] SR BTS ASY					
5 XX SCREW, #6-32X.250 BHD, PH/SL (-49 OPT)				BRASS		NICKEL PLATE										3 PLACES ± --- ± .005		± .005 INCH		CHECKED BY DATE		CS W/COVER, INSUL. FT					
4 XX SCREW, #6-32X.250 BHD, PH/SL (STD.)				STEEL		ZN, CLEAR CHROMATE										2 PLACES ± 0.13 ± .01		± .01 INCH		J. MACNEIL 2006/08/18							
3 XX TERM FT, #6-32				BRASS		TIN PLATE										1 PLACE ± 0.3 ± ---		± --- INCH		APPROVED BY DATE							
2 1 COVER, HINGE				PBT, 30% GF		BLACK										ANGULAR ± 2 °		ANGULAR ± 2 ° INCH		J. MACNEIL 2006/08/18		MOLEX MOLEX INCORPORATED					
1 1 INSULATOR, SR BTS CSINSL, MO MTG.				PBT, 30% GF		BLACK														MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
																				SEE SHT. 2		SD-38729-047		1 OF 2			
																				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
																				SIZE B							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

38729-1070