

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1201080509

Status:


Active

Overview:

Brad Industrial Ethernet Solutions

Description:

Micro-Change (M12) Double-Ended Cordset, 4 Poles, Male (90°) to Male (90°), Green TPU WSOR Cable, 22 AWG, 2.0m (6.56') Length



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Cordsets
Series	120108
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Industrial Ethernet Solutions
Product Name	Micro-Change (M12)
Protocol	EtherNet
Type	Double Ended
UPC	78172545792
Physical	
Cable Diameter	6.80mm (.268")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Green
Coupling Style	Threaded
Gender	Male-Male
Keyway	D-coded
LED Indicator	No
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Coupling Nut	Brass
Material - Plating Mating	Gold
Net Weight	254.000/g
Orientation	90° to 90°
Poles	4
Temperature Range - Operating	-20° to +60°C
Wire Size AWG	22
Wire/Cable Type	Shielded TPE/AWM 21215
Electrical	
Current - Maximum per Contact	1.5A
Voltage - Maximum	30V
Material Info	
Engineering Number	E11A06312M020
Reference - Drawing Numbers	
Sales Drawing	SD-120108-073-001

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2021)4569-DC (8 July 2021)	
Lead	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Reviewed
RoHS Phthalates	Not Contained

Search Parts in this Series

120108 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1201080509