

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202540003

Status:

Active

Overview:

Contrinex Inductive and Photoelectric

Description:

Contrinex Photoelectric Sensor, C12 (13.5 x 21.8mm) Housing, Through-Beam (Receiver), 0 - 2000mm Operating Distance, NPN, Dark-ON, 0.2m 3-wire PVC Cable, 3-pin M8 Connector



Documents:

Product Specification 1202540003-000 (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

General	
Product Family	Sensors
Series	120254
IP Rating	IP67
Operating Principle	Through-Beam (Receiver)
Overview	Contrinex Inductive and Photoelectric
Product Category	Photoelectric Sensors
Product Name	Contrinex
Type	Photoelectric
UPC	191130066193
Physical	
Connection	Cable (PVC 0.2m, 3-wire), Connector (M8, 3-pin)
Housing Size	13.5 x 21.8mm
Material - Housing	ABS
Material - Window	PMMA
Operating Distance	0 - 2000mm
Output	Dark-ON
Sensor Housing Size	C12
Temperature Range - Operating	-20° to +50°C
Electrical	
Polarity	NPN
Switching Frequency	≤ 800 Hz
Material Info	
Engineering Number	LLR-C12PA-NMV-302
Reference - Drawing Numbers	
Product Specification	1202540003-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

120254 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

120254-0003