

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1731090186](#)
Status: **Active**
Overview: [FCT D-Sub Connectors](#)
Description: FCT Standard-Density D-Sub Connector, Male, Right-Angle, PCB Through Hole, Gold Plating, 50 Mating Cycles, Riveted Metal Bracket and Clinch Nut, 9 Circuits


Documents:
[Datasheet \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family D-Sub Products
Series [173109](#)
IP Rating IP20
Overview [FCT D-Sub Connectors](#)
Product Category D-Sub Connector
Product Name FCT Products
Type Standard Density
UPC 889056486682

Physical
Circuits (Loaded) 9
Circuits (maximum) 9
Color - Resin White
Durability (mating cycles max) 50
Gender Male
Material - Contact Copper Alloy
Material - Resin PBT
Material - Shell Steel
Net Weight 9.500/g
Number of Rows 2
Orientation Right-Angle
PC Tail Length 11.10mm
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Carton
Panel Mount Rear
Panel Mount Method Thread-In
Pitch - Mating Interface 2.84mm
Pitch - Termination Interface 2.54mm
Plating - Contact Gold over Nickel
Plating - Shell Tin
Polarized to Mating Part Yes
Polarized to PCB Yes
Ports 1
Shielded Yes
Temperature Range - Operating -55° to +125°C
Termination Style Through Hole
Waterproof / Dustproof No
Waterproof / Dustproof Type IP20

Electrical
Current - Maximum per Contact 7.5A

Material Info
Engineering Number F09P5G3-1002



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant with Exemption 6(a)-I,6(c)	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[173109 Series](#)

Mates With
FCT Standard-Density D-Sub, Size 1, 9 Position, Socket

This document was generated on 02/23/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[173109-0186](#)