

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1731090692](#)
Status: **Active**
Overview: [FCT D-Sub Connectors](#)
Description: FCT Standard-Density D-Sub Connector, Male, Right-Angle, PCB Through Hole, Gold over Nickel Phosphorus Plating, 500 Mating Cycles, 9 Circuits

Documents:

[Datasheet \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

General

Product Family D-Sub Products
Series [173109](#)
IP Rating IP20
Overview [FCT D-Sub Connectors](#)
Product Category D-Sub Connector
Product Name FCT Products
Type Standard Density
UPC 191128904759

Physical


Circuits (Loaded) 9
Circuits (maximum) 9
Color - Resin White
Durability (mating cycles max) 500
Gender Male
Material - Contact Copper Alloy
Material - Resin PBT
Material - Shell Steel
Net Weight 5.800/g
Number of Rows 2
Orientation Right-Angle
PC Tail Length 11.10mm
PCB Locator No
PCB Retention None
PCB Thickness - Recommended 1.60mm
Packaging Type Carton
Panel Mount Rear
Panel Mount Method Flange
Pitch - Mating Interface 2.84mm
Pitch - Termination Interface 2.54mm
Plating - Contact Gold over Nickel Phosphorus
Plating - Shell Tin
Polarized to Mating Part Yes
Polarized to PCB Yes
Ports 1
Shielded Yes
Temperature Range - Operating -55° to +125°C
Termination Style Through Hole
Waterproof / Dustproof No
Waterproof / Dustproof Type IP20

Electrical

Current - Maximum per Contact 7.5A

Material Info

Engineering Number F09P5G1A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[173109](#) Series

Mates With

FCT Standard-Density D-Sub, Size 1, 9
Position, Socket

This document was generated on 07/26/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[173109-0692](#)