This document was generated on 08/25/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 2163002123

Status: Active

Overview: Off-the-Shelf Pre-Crimped Leads

Description: Pre-Crimped Lead MX150 Female-to-MX150 Female, Tin (Sn) Plating, 225.00mm Length, 14 AWG, Red

Series image - Reference only

Documents:

Drawing (PDF)
Datasheet (PDF)
RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	216300
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	MX150 Crimp Terminals
Overview	Off-the-Shelf Pre-Crimped Leads
Product Name	MX150
UPC	195842070530
Physical	
Cable Length	225.00mm
Circuits (Loaded)	1
Color - Resin	Red
Gender	Female-Female
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Net Weight	6.246/g
Packaging Type	Bag
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.70mm max.
Wire Size AWG	14
Wire/Cable Type	TXL
Electrical	
Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC
Material Info	
Reference - Drawing Numbers	
Sales Drawing	2163001121-000

EU ELV
Not Relevant

EU RoHS | **China RoHS**
Compliant

REACH SVHC
Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free Status
Low-Halogen

For more information, please visit Contact US

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
216300 Series

Use With
MX150 Dual Row Housing 33472 . MX150 Single Row Housing 33471 . MX150 Hybrid Housing 33476

This document was generated on 08/25/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:
216300-2123