

Datasheet for 76650-0014

General Information

Part Number:	76650-0014
Manufacturer:	Molex / Waldom
Title:	Mini-Fit Jr. Power Connector Kit
Description:	Panel Mount Plug and Receptacle
Product Family:	Mini-Fit Jr.™
Certificates:	(Molex parts within this kit) EU and China RoHS Compliant, UL, CSA and TUV
Country of Origin:	Kit assembled in U.S.A.

Specifications

Design

Configuration:	Wire-to-Wire
Pitch:	4.20mm (.165")
Connector Type:	Plug and Receptacle

Mounting

Orientation:	Panel Mount and Free Hanging
Circuit Sizes:	2, 3, 4, 6, 8, 10, 12, 14, 16, 18 and 20
Current Rating:	(3 - 9) Amps dependent on AWG and circuit size
Voltage:	600 Volts
Wire size:	24-18 AWG

Product Highlights

The Mini-Fit Jr. Series is designed for high current/high density applications. The Mini-Fit Jr. is appropriate for both power and signal applications as it can carry currents of up to 9 amps per circuit. The Mini-Fit product family accepts the same terminals and application tooling, further reducing your design and qualification effort.

Features and Benefits

- Fully isolated terminals
- Positive housing locks
- Four point of contact for reliability
- Low engagement force terminals

Applications

- Security and Alarms
- Vending and Gaming Machines
- White Goods
- Production Equipment
- Broadcast Equipment
- Telecom Infrastructure

Datasheet for 76650-0014

Bill of Materials for Part No. 76650-0014

Molex Part No.	Country of Origin	Description	Quantity in Kit
39-00-0039	USA	Crimp Type Female Socket Terminals, 24-18 AWG	100
39-00-0041	USA	Crimp Type Male Pin Terminals, 24-18 AWG	100
39-01-2020	USA	2 Circuit Free Hanging Receptacle, 4.20mm/.165" Pitch	5
39-01-2040	USA	4 Circuit Free Hanging Receptacle, 4.20mm/.165" Pitch	5
39-01-2060	USA	6 Circuit Free Hanging Receptacle, 4.20mm/.165" Pitch	5
39-01-2080	USA	8 Circuit Free Hanging Receptacle, 4.20mm/.165" Pitch	5
39-01-2100	USA	10 Circuit Free Hanging Receptacle, 4.20mm/.165" Pitch	5
39-01-2120	USA	12 Circuit Free Hanging Receptacle, 4.20mm/.165" Pitch	4
39-01-2140	USA	14 Circuit Free Hanging Receptacle, 4.20mm/.165" Pitch	3
39-01-2160	China	16 Circuit Free Hanging Receptacle, 4.20mm/.165" Pitch	3
39-01-2180	USA	18 Circuit Free Hanging Receptacle, 4.20mm/.165" Pitch	3
39-01-2200	USA	20 Circuit Free Hanging Receptacle, 4.20mm/.165" Pitch	3
39-01-2021	USA	2 Circuit Panel Mount Plugs, 4.20mm/.165" Pitch	5
39-01-2041	USA	4 Circuit Panel Mount Plugs, 4.20mm/.165" Pitch	5
39-01-2061	USA	6 Circuit Panel Mount Plugs, 4.20mm/.165" Pitch	5
39-01-2081	Japan	8 Circuit Panel Mount Plugs, 4.20mm/.165" Pitch	5
39-01-2101	USA	10 Circuit Panel Mount Plugs, 4.20mm/.165" Pitch	5
39-01-2121	USA	12 Circuit Panel Mount Plugs, 4.20mm/.165" Pitch	4
39-01-2141	USA	14 Circuit Panel Mount Plugs, 4.20mm/.165" Pitch	3
39-01-2161	Korea	16 Circuit Panel Mount Plugs, 4.20mm/.165" Pitch	3
39-01-2181	USA	18 Circuit Panel Mount Plugs, 4.20mm/.165" Pitch	3
39-01-2201	USA	20 Circuit Panel Mount Plugs, 4.20mm/.165" Pitch	3

Recommended Molex Tool(s) for Part No. 76650-0014*

Molex Part No.	Country of Origin	Description
63819-0900 *	Sweden	Hand Crimp Tool
11-03-0044 *	Sweden	Extraction Tool

*Tool(s) not included in kit. Tool(s) ordered separately.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

76650-0014