

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2011962220

Status:


Active

Overview:

Spot-On Wire-to-Board Connector System

Description:

Spot-On Wire-to-Board Receptacle Housing, 2.00mm Pitch, Dual Row, 22 Circuits, Natural



Series image - Reference only

Documents:	
3D Model	Application Specification 2011960000-A00 (PDF)
Drawing (PDF)	Application Specification 2011960000-A01 (PDF)
3D Model (PDF)	Packaging Specification 2011969200-200 (PDF)
Product Specification 2011960000-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	201196
Application	Signal, Wire-to-Board
Overview	Spot-On Wire-to-Board Connector System
Product Name	Spot-On
UPC	191128245975
Physical	
Circuits (maximum)	22
Color - Resin	Natural
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	1529.000/mg
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C
Material Info	
Reference - Drawing Numbers	
Application Specification	2011960000-A00, 2011960000-A01
Packaging Specification	2011969200-200
Product Specification	2011960000-PS-000
Sales Drawing	2011962300-SD-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

201196 Series

Mates With

Spot-On Header 201197

Use With

Receptacle Terminal 2011956000 , TPA Retainer 2011964110

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[201196-2220](#)