

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2086592870

Status:

Active

Overview:

iGrid Wire-to-Board Dual-Row System

Description:

2.00mm Pitch, iGrid PCB Header, Dual Row, Right-Angle, Through Hole, 0.76µm Gold (Au) Plating, Positive Lock, 28 Circuits, Tray, 3.20mm PC Tail Length, Natural

Documents:	
3D Model	Product Specification 5016461000-PS-000 (PDF)
3D Model (PDF)	Packaging Specification 2086599200-SPK-200 (PDF)
Drawing (PDF)	Datasheet (PDF)
Product Specification 5016460000-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General


Product Family	PCB Headers
Series	208659
Application	Signal, Wire-to-Board
Overview	iGrid Wire-to-Board Dual-Row System
Product Name	iGrid
UPC	193264111794

Physical

Breakaway	No
Circuits (Loaded)	28
Circuits (maximum)	28
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Resin	Polyamide
Net Weight	2180.000/mg
Number of Rows	2
Orientation	Right Angle
PC Tail Length	3.20mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.20mm, 1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	2.0A
-------------------------------	------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

208659 Series

Mates With

iGrid Receptacle Housing [501646](#)

Voltage - Maximum	250V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Packaging Specification	2086599200-SPK-200
Product Specification	5016460000-PS-000, 5016461000-PS-000
Sales Drawing	2086590000-SD-000

This document was generated on 12/21/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

208659-2870