

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [1511194240](#)  
**Status:** **Active**  
**Overview:** Milli-Grid Connector System  
**Description:** 2.00mm Pitch, Milli-Grid PCB Header, Dual Row, Right-Angle, Through Hole, 0.38µm Gold (Au) Plating, without Peg, 3.60mm PC Tail Length, without Pick and Place Tape, 40 Circuits, Glow-Wire Capable, Tube

**Documents:**

|                                                                  |                                                                  |
|------------------------------------------------------------------|------------------------------------------------------------------|
| <a href="#">3D Model</a>                                         | <a href="#">Application Specification 503940002-AS-000 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                                    | <a href="#">Packaging Specification PK-151119-0001-001 (PDF)</a> |
| <a href="#">3D Model (PDF)</a>                                   | <a href="#">Packaging Specification PK-151119-3000-001 (PDF)</a> |
| <a href="#">Product Specification PS-151117-0001-001 (PDF)</a>   | <a href="#">Datasheet (PDF)</a>                                  |
| <a href="#">Application Specification 503940001-AS-000 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>             |

**Agency Certification**

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                |                                             |
|----------------|---------------------------------------------|
| Product Family | PCB Headers                                 |
| Series         | <a href="#">151119</a>                      |
| Application    | Board-to-Board, Signal, Wire-to-Board       |
| Overview       | <a href="#">Milli-Grid Connector System</a> |
| Product Name   | Milli-Grid                                  |
| UPC            | 889056753197                                |

**Physical**

|                                |                        |
|--------------------------------|------------------------|
| Breakaway                      | No                     |
| Circuits (Loaded)              | 40                     |
| Circuits (maximum)             | 40                     |
| Color - Resin                  | Black                  |
| First Mate / Last Break        | No                     |
| Flammability                   | 94V-0                  |
| Glow-Wire Capable              | Yes                    |
| Guide to Mating Part           | No                     |
| Keying to Mating Part          | None                   |
| Lock to Mating Part            | Yes                    |
| Material - Metal               | Copper Alloy           |
| Material - Plating Mating      | Gold                   |
| Material - Plating Termination | Tin                    |
| Material - Resin               | Liquid Crystal Polymer |
| Net Weight                     | 2.153/g                |
| Number of Rows                 | 2                      |
| Orientation                    | Right Angle            |
| PC Tail Length                 | 3.60mm                 |
| PCB Locator                    | No                     |
| PCB Retention                  | None                   |
| PCB Thickness - Recommended    | 2.60mm                 |
| Packaging Type                 | Tube                   |
| Pitch - Mating Interface       | 2.00mm                 |
| Pitch - Termination Interface  | 2.00mm                 |
| Plating min - Mating           | 0.380µm                |
| Plating min - Termination      | 2.000µm                |
| Polarized to Mating Part       | Yes                    |
| Polarized to PCB               | Yes                    |
| Shrouded                       | Yes                    |
| Stackable                      | No                     |



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[151119](#) Series

**Mates With**

Milli-Grid Receptacle Housing [151192](#) ,  
[51110](#) <br>Milli-Grid PCB Receptacles  
[78787](#) , [78788](#) , [79107](#) , [79109](#)

|                                |                |
|--------------------------------|----------------|
| Surface Mount Compatible (SMC) | Yes            |
| Temperature Range - Operating  | -55° to +105°C |
| Termination Interface: Style   | Through Hole   |

**Electrical**

|                               |         |
|-------------------------------|---------|
| Current - Maximum per Contact | 2.0A    |
| Voltage - Maximum             | 125V AC |

**Solder Process Data**

|                                                |          |
|------------------------------------------------|----------|
| Duration at Max. Process Temperature (seconds) | 010      |
| Lead-freeProcess Capability                    | SMC&WAVE |
| Max. Cycles at Max. Process Temperature        | 001      |
| Process Temperature max. C                     | 260      |

**Material Info**

**Reference - Drawing Numbers**

|                           |                                        |
|---------------------------|----------------------------------------|
| Application Specification | 503940001-AS-000, 503940002-AS-000     |
| Packaging Specification   | PK-151119-0001-001, PK-151119-3000-001 |
| Product Specification     | PS-151117-0001-001                     |
| Sales Drawing             | SD-151119-0001-001                     |

This document was generated on 09/02/2021

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[151119-4240](#)