

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0015910347

Status:

Active

Overview:

C-Grid Connector Products

Description:

2.54mm Pitch C-Grid Breakaway Header, Surface Mount, Dual Row, Vertical, 34 Circuits, 0.38µm Gold (Au) Selective Plating, with 3.30mm PCB Locator Pegs, with 8.13mm Mating Pin Length

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-71308-001 (PDF)

Application Specification 713080001-AS-000 (PDF)

Packaging Specification 713080001-PK-000 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

71308

Application

Board-to-Board, Signal, Wire-to-Board

Overview

C-Grid Connector Products

Product Name

C-Grid

UPC

800754652155

Physical

Breakaway

Yes

Circuits (Loaded)

34

Circuits (maximum)

34

Color - Resin

Black

Durability (mating cycles max)

50

Flammability

94V-0

Glow-Wire Capable

No

Lock to Mating Part

None

Material - Metal

Phosphor Bronze

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

2.621/g

Number of Rows

2

Orientation

Vertical

PCB Locator

Yes

PCB Retention

Yes

Packaging Type

Tube

Pitch - Mating Interface

2.54mm

Plating min - Mating

0.381µm

Plating min - Termination

1.905µm

Polarized to Mating Part

No

Polarized to PCB

No

Shrouded

No

Stackable

Yes

Temperature Range - Operating

-40° to +105°C

Termination Interface: Style

Surface Mount


Electrical

Current - Maximum per Contact

3.0A

Voltage - Maximum

250V



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series
71308 Series

Solder Process Data

Duration at Max. Process Temperature (seconds)	030
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

Material Info

Engineering Number	71308-5134
--------------------	------------

Reference - Drawing Numbers

Application Specification	713080001-AS-000
Packaging Specification	713080001-PK-000
Product Specification	PS-71308-001
Sales Drawing	713080000-SD-000

This document was generated on 01/03/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

15-91-0347