

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0354216802](#)
Status: **Active**
Description: Tab Crimp Terminal 35421, AVS

Documents:

Drawing (PDF)	Packaging Specification PK-35421-001-001 (PDF)
Product Specification PS-35282-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-35385-001-001 (PDF)	

General

Product Family	Crimp Terminals
Series	35421
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Product Name	N/A
UPC	800753943131

Physical

Gender	Female
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.306/g
Packaging Type	Reel
Plating min - Mating	0.813µm
Plating min - Termination	0.813µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.60mm max.
Wire Size AWG	16, 18
Wire Size mm²	N/A


Solder Process Data

Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	N/A
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-35421-001-001
Product Specification	PS-35282-001-001, PS-35385-001-001
Sales Drawing	SD-35421-001, SD-35421-6X02



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[35421](#) Series

Mates With

[35420](#)

Use With

[35378](#) , [35374](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[35421-6802](#)