

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0355071600

Status:

Active

Overview:

Sherlock Wire-to-Board Connector System

Description:

2.00mm Pitch Sherlock Wire-to-Board Housing, Natural, 16 Circuits

Documents:

3D Model

Product Specification PS-35507-003-001 (PDF)

Drawing (PDF)

Packaging Specification 355070200-100 (PDF)

Product Specification PS-35507-001-001 (PDF)

Packaging Specification PK-35507-001 (PDF)

Product Specification PS-35507-002-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

General

Product Family

Crimp Housings

Series

35507

Application

Signal, Wire-to-Board

Overview

Sherlock Wire-to-Board Connector System

Product Name

Sherlock

UPC

756054562123

Physical

Circuits (maximum)

16

Circuits Detail

16

Color - Resin

Natural

Flammability

94V-0

Gender

Receptacle

Glow-Wire Capable

No

Keying to Mating Part

None

Lock to Mating Part

Yes

Material - Resin

Polyester

Net Weight

0.612/g

Number of Rows

1

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

2.00mm

Polarized to Mating Part

Yes

Stackable

No

Temperature Range - Operating

-40° to +105°C

Electrical

Current - Maximum per Contact

2.0A

Material Info

Reference - Drawing Numbers

Packaging Specification


355070200-100, PK-35507-001

Product Specification

PS-35507-001-001, PS-35507-002-001, PS-35507-003-001

Sales Drawing

SD-35507-001, SD-35507-001-001, SD-35507-001-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

35507 Series

Mates With

Sherlock Wire-to-Board Header 35362 , 35363

Use With

2.00mm Pitch Crimp Terminal 50212

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

35507-1600