

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0622018609

Status:

Active

Overview:

Application Tooling

Description:

Press-In Tool for Vertical Header 7-Row, 10-Column

Documents:

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Function

Geographic Area

Level of Automation

More Detailed Tech Information

Overview

Product Name

Tool Type

UPC

Warranty Disclaimer

Application Tooling

207123

See Tooling Specification (PDF) Above, Press-In Tool Insertion

Global

Manual

applicationtooling@molex.com

Application Tooling

PremiumGrade

Press-Fit Insertion Tool

822350874656

CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight


138.470/g

Material Info

Reference - Drawing Numbers

Application Tooling Documents

ATS-622018609, TM-622018699



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China RoHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

207123 Series

Use With

GbX I-Trac Backplane Signal Module, 76015 Series

Application Tooling Description	FAQ Product #
GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Unguided, Open Ends, 7 Rows, 10 Columns, 140 Circuits, Mating Pin Length 3.90mm	760151102
GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Unguided, Open Ends, 7 Rows, 10 Columns, 140 Circuits, Mating Pin Length 4.70mm	760151103

GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Unguided, Open Ends, 7 Rows, 10 Columns, 140 Circuits, Mating Pin Length 5.70mm	760151104
GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Left Guide, Right Open, 7 Rows, 10 Columns, 140 Circuits, Mating Pin Length 4.70mm, Lead-Free	760153103
GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Left Guide, Right Open, 7 Rows, 10 Columns, 140 Circuits, Mating Pin Length 5.70mm, Lead-Free	760153104
GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Right Guide, Left Open, 7 Rows, 10 Columns, 140 Circuits, Mating Pin Length 4.70mm, Lead-Free	760155103
GbX I-Trac Vertical Header Module, 1.85mm by 3.70mm Pitch, Right Guide, Left Open, 7 Rows, 10 Columns, 140 Circuits, Mating Pin Length 5.70mm, Lead-Free	760155104

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62201-8609](#)