

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1552100057

Status:

Active

Overview:

Flamar Standard and Custom Cables for Industrial Automation

Description:

Flamar Sensor Cable, PVC Jacket, Unshielded, 3 Circuits, 0.34mm² / 22 AWG, 4.80mm (.189") Diameter, 1500.0m (4921.26') Length, Gray


Documents:

Product Specification 1552100001-P1E (PDF)

RoHS Certificate of Compliance (PDF)

Brochure (PDF)

General	
Product Family	Cable
Series	155210
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	Flamar Standard and Custom Cables for Industrial Automation
Product Name	Flamar, Signal and Control
UPC	889056449854
Physical	
Bending Radius - Minimum	> 15xOD
Cable Length	1500.0m
Circuits (Loaded)	3
Color - Cable Jacket	Gray
Insulation	TPE
Material - Outer Jacket	PVC
Net Weight	0.010/g
Outer Jacket Diameter	4.80mm
Packaging Type	Reel
Temperature Range - Operating	+5° to +80°C
Wire Size AWG	22
Wire Size mm²	0.34
Wire/Cable Type	UL AWM 2464 / CSA
Electrical	
Current - Maximum per Contact	Contact Molex
Voltage - Maximum	300V
Material Info	
Engineering Number	1X1500M
Reference - Drawing Numbers	
Product Specification	1552100001-P1E



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

155210 Series

Use With

Nano-Change (M8) 120091 , Micro-Change (M12) 120071 , Ultra-Lock (M12) 120085

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155210-0057](#)