

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1552100069](#)  
**Status:** **Active**  
**Overview:** [Flamar Standard and Custom Cables for Industrial Automation](#)  
**Description:** Flamar Sensor Cable, PVC Jacket, Unshielded, 4 Circuits, 0.34mm<sup>2</sup> / 22 AWG, 5.10mm (.201") Diameter, 1500.0m (4921.26') Length, Gray

**Documents:**

[Product Specification 1552100001-P1E \(PDF\)](#)      [RoHS Certificate of Compliance \(PDF\)](#)  
[Brochure \(PDF\)](#)

**General**

|                         |                                                                             |
|-------------------------|-----------------------------------------------------------------------------|
| Product Family          | Cable                                                                       |
| Series                  | <a href="#">155210</a>                                                      |
| Crimp Quality Equipment | Yes                                                                         |
| Geographic Area         | Global                                                                      |
| Overview                | <a href="#">Flamar Standard and Custom Cables for Industrial Automation</a> |
| Product Name            | Flamar, Signal and Control                                                  |
| UPC                     | 889056450072                                                                |

**Physical**

|                               |                   |
|-------------------------------|-------------------|
| Bending Radius - Minimum      | > 15xOD           |
| Cable Length                  | 1500.0m           |
| Circuits (Loaded)             | 4                 |
| Color - Cable Jacket          | Gray              |
| Insulation                    | TPE               |
| Material - Outer Jacket       | PVC               |
| Net Weight                    | 0.010/g           |
| Outer Jacket Diameter         | 5.10mm            |
| Packaging Type                | Reel              |
| Temperature Range - Operating | +5° to +80°C      |
| Wire Size AWG                 | 22                |
| Wire Size mm <sup>2</sup>     | 0.34              |
| Wire/Cable Type               | UL AWM 2464 / CSA |

**Electrical**


|                               |               |
|-------------------------------|---------------|
| Current - Maximum per Contact | Contact Molex |
| Voltage - Maximum             | 300V          |

**Material Info**

|                    |         |
|--------------------|---------|
| Engineering Number | 1X1500M |
|--------------------|---------|

**Reference - Drawing Numbers**

|                       |                |
|-----------------------|----------------|
| Product Specification | 1552100001-P1E |
|-----------------------|----------------|



Series image - Reference only

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

**China RoHS**

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Reviewed |
| ELV             | Not Reviewed |
| RoHS Phthalates | Not Reviewed |

**Search Parts in this Series**

[155210](#) Series

**Use With**

Nano-Change (M8) [120091](#) , Micro-Change (M12) [120071](#) , Ultra-Lock (M12) [120085](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

155210-0069