

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2035570507

Status:

Active

Overview:

Pico-Clasp Wire-to-Board Connectors

Description:

1.00mm Pitch, Pico-Clasp PCB Header, Single Row, Vertical, Surface Mount, 0.76µm Gold Plated, Friction Lock, 5 Circuits, Natural

Documents:

3D Model	Product Specification 5013301000-PS-CHI-002 (PDF)
Drawing (PDF)	Product Specification 5013301000-PS-JAP-002 (PDF)
3D Model (PDF)	Application Specification 5013300000-AS-000 (PDF)
Product Specification 5013300000-PS-002 (PDF)	Packaging Specification 2035579200-200 (PDF)
Product Specification 5013301000-PS-002 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	PCB Headers
Series	203557
Application	Signal, Wire-to-Board
Overview	Pico-Clasp Wire-to-Board Connectors
Product Name	Pico-Clasp
UPC	191128167482

Physical

Breakaway	No
Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Polyamide
Net Weight	120.760/mg
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Plating min - Mating	0.760µm
Plating min - Termination	0.102µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Robotic Placement	Vacuum Pick-Up Tape
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	100V AC (RMS)/DC



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

203557 Series

Mates With

Pico-Clasp Female Housing 501330

Material Info

Reference - Drawing Numbers

Application Specification	5013300000-AS-000
Packaging Specification	2035579200-200
Product Specification	5013300000-PS-002, 5013301000-PS-002, 5013301000-PS-CHI-002, 5013301000-PS-JAP-002
Sales Drawing	2035570000-SD-000

This document was generated on 02/03/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

203557-0507