

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **5013300500**
Status: **Active**
Overview: Pico-Clasp Wire-to-Board Connectors
Description: 1.00mm Pitch, Pico-Clasp Low-Halogen Receptacle Crimp Housing, Single Row, Friction Lock, 5 Circuits, White

Documents:

3D Model	Product Specification 5013301000-PS-002 (PDF)
3D Model (PDF)	Product Specification 5013301000-PS-003 (PDF)
Drawing (PDF)	Product Specification 5013301000-PS-004 (PDF)
Product Specification 5013300000-PS-001 (PDF)	Product Specification 5013301000-PS-JAP-002 (PDF)
Product Specification 5013300000-PS-002 (PDF)	Application Specification 5013300000-AS-000 (PDF)
Product Specification 5013300000-PS-003 (PDF)	Application Specification 5013300000-AS-001 (PDF)
Product Specification 5013300000-PS-004 (PDF)	Packaging Specification SPK-501330-001-001 (PDF)
Product Specification 5013301000-PS-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL E29179

Application tooling part link

Application Tooling Part Link 63813-1700

General

Product Family Crimp Housings
 Series [501330](#)
 Application Signal, Wire-to-Board
 Overview [Pico-Clasp Wire-to-Board Connectors](#)
 Product Name Pico-Clasp
 UPC 822348528967

Physical

Circuits (maximum) 5
 Color - Resin White
 Gender Receptacle
 Glow-Wire Capable No
 Keying to Mating Part None
 Lock to Mating Part Yes
 Material - Resin Nylon
 Net Weight 39.300/mg
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 1.00mm
 Pitch - Termination Interface 1.00mm
 Polarized to Mating Part Yes
 Stackable No
 Temperature Range - Operating -40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification 5013300000-AS-000, 5013300000-AS-001
 Packaging Specification SPK-501330-001-001
 Product Specification 5013300000-PS-001, 5013300000-PS-002, 5013300000-PS-003, 5013300000-PS-004, 5013301000-PS-001, 5013301000-PS-002, 5013301000-PS-003, 5013301000-PS-004, 5013301000-PS-JAP-002



Series image - Reference only

**EU ELV
Compliant**

**EU RoHS
Compliant**

REACH SVHC
Not Contained Per -
D(2021)4569-DC (8
July 2021)

**Halogen-Free
Status**

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS
ELV

RoHS Phthalates

China RoHS

Green Image
Compliant
Not Contained

Search Parts in this Series

[501330](#) Series

Mates With

Pico-Clasp Vertical Header [501331](#) , [504449](#)
 , [203556](#) , [203557](#) . Pico-Clasp Right-Angle
 Header [501568](#) , [202396](#) , [203558](#) , [203559](#)

Use With

Pico-Clasp Female Terminal [501334](#) (Tin),
[501193](#) (Gold)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool for [638131700](#)
 Pico-Clasp Wire-to-
 Board Terminals,
 28-32 AWG

This document was generated on 01/24/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[501330-0500](#)