

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1552200066](#)
Status: **Active**
Overview: [Flamar Standard and Custom Cables for Industrial Automation](#)
Description: Flamar Sensor Cable, WSOR Jacket, Unshielded, 4 Circuits, 0.34mm² / 22 AWG, 5.10mm (.201") Diameter, 1500.0m (4921.26') Length, Black

Documents:

[Product Specification 1552200001-P1E \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

UL E172949

General

Product Family Cable
Series [155220](#)
Crimp Quality Equipment Yes
Geographic Area Global
Overview [Flamar Standard and Custom Cables for Industrial Automation](#)
Product Name Flamar, Signal and Control
UPC 889056457903

Physical

Bending Radius - Minimum > 7.5xOD
Cable Length 1500.0m
Circuits (Loaded) 4
Color - Cable Jacket Black
Insulation TPE
Material - Outer Jacket WSOR
Net Weight 0.036/kg
Outer Jacket Diameter 5.10mm
Packaging Type Reel
Temperature Range - Operating -25° to +80°C
Wire Size AWG 22
Wire Size mm² 0.34
Wire/Cable Type UL AWM 21215 / CSA

Electrical


Current - Maximum per Contact Contact Molex
Voltage - Maximum 600V

Material Info

Engineering Number B30-4-1X1500M

Reference - Drawing Numbers

Product Specification 1552200001-P1E



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[155220](#) Series

Use With

Nano-Change (M8) [120091](#) , Micro-Change (M12) [120071](#) , Ultra-Lock (M12) [120085](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[155220-0066](#)