

The Future of Analog IC Technology

DESCRIPTION

The MP5075L provides up to 1A of load protection over a 3V to 5.5V voltage range with a small $R_{DS(ON)}$ in a space-saving package. The MP5075L is a very high-efficiency and space-saving solution for notebooks, tablets, and other portable and battery-operated applications.

With a fixed soft-start function, the MP5075L can prevent inrush current during circuit startup. The MP5075L also provides output discharge functions, over-current protection (OCP), and thermal shutdown features.

The max load at the output (source) is currentlimited. This is accomplished by utilizing sense FET topology.

An internal charge pump drives the gate of the power device, allowing for a very low on-resistance DMOS power FET of just $80m\Omega$.

The MP5075L is available in a space-saving SOT563 (1.6mmx1.6mm) package.

FEATURES

- Integrated 80mΩ Low R_{DS(ON)} MOSFETs
- Wide VIN Range from 3V to 5.5V
- <5µA Shutdown Current
- Typical 1.4A Current Limit
- Output Discharge Function
- Internal Fixed 450µs Soft-Start Time
- <200ns Short-Circuit Protection Response Time
- Thermal Protection
- Available in a SOT563 (1.6mmx1.6mm) Package

APPLICATIONS

- Notebook and Tablet Computers
- Portable Devices
- Solid-State Drives
- Handheld Devices
- USB Power Distribution
- USB Dongles

All MPS parts are lead-free, halogen-free, and adhere to the RoHS directive. For MPS green status, please visit the MPS website under Quality Assurance. "MPS" and "The Future of Analog IC Technology" are registered trademarks of Monolithic Power Systems, Inc.

TYPICAL APPLICATION





ORDERING INFORMATION

Part Number*	Package	Top Marking
MP5075LGTF	SOT563	See Below

* For Tape & Reel, add suffix –Z (e.g. MP5075LGTF–Z)

TOP MARKING

AWPY

LLL

AWP: Product code of MP5075LGTF Y: Year code LLL: Lot number

PACKAGE REFERENCE





ABSOLUTE MAXIMUM RATINGS (1)

VIN	0.3V to +6.5V
VOUT	0.3V to +6.5V
EN	0.3V to +6.5V
Junction temperature	150°C
Lead temperature	260°C
Continuous power dissipatio	on (T _A = +25°C) ⁽²⁾
	1W

Recommended Operating Conditions ⁽³⁾

Supply voltage (VIN)	3V to 5.5V
Output voltage (VOUT)	3V to 5.5V
Output current (I _{OUT})	1A
Operating junction temp. (T _J)	-40°C to +125°C

Thermal Resistance ⁽⁴⁾ θ_{JA} θ_{JC}

SOT563 130..... 60... °C/W

NOTES:

- 1) Exceeding these ratings may damage the device.
- 2) The maximum allowable power dissipation is a function of the maximum junction temperature T_J (MAX), the junction-toambient thermal resistance θ_{JA} , and the ambient temperature T_A. The maximum allowable continuous power dissipation at any ambient temperature is calculated by P_D (MAX) = (T_J (MAX)-T_A)/ θ_{JA} . Exceeding the maximum allowable power dissipation produces an excessive die temperature, causing the regulator to go into thermal shutdown. Internal thermal shutdown circuitry protects the device from permanent damage.
- The device is not guaranteed to function outside of its operating conditions.
- 4) Measured on JESD51-7, 4-layer PCB.



ELECTRICAL CHARACTERISTICS

VIN = 5V, T_J = -40°C to 125°C ⁽⁵⁾, typical value is tested at T_J = 25°C, unless otherwise noted.

Parameters	Symbol	Condition	Min	Тур	Max	Units		
Input and Supply Voltage Range								
Input voltage	Vin		3		5.5	V		
Supply Current								
Off-state leakage current	IOFF	VIN = 5V, EN = 0			5	μA		
VIN standby surrant	ISTBY	VIN = 5V, EN = 0		0.1	5	μA		
		VIN = 5V, enable, no load		230	300			
Power FET								
On resistance	Proof	VIN = 5V		80		mΩ		
	NDSON	VIN = 3.3V		110				
Thermal Shutdown and Recovery								
Shutdown temperature (6)	T _{STD}			150		°C		
Hysteresis ⁽⁶⁾	T _{HYS}			30		°C		
Under-Voltage Protection (UVLO)								
VIN under-voltage lockout threshold	VIN_UVLO	UVLO rising threshold	2.3	2.6	2.9	V		
UVLO hysteresis	VUVLO-HYS			200		mV		
Soft Start (SS)								
SS time	Tss	0% to 100%		450		μs		
Enable (EN)								
EN rising threshold	Venh		1.3	1.5	1.7	V		
EN hysteresis	Ven-hys			200		mV		
EN pull-down resistor	Rpud			1		MΩ		
ILIM								
Current limit	louт		1.2	1.4	1.6	А		
Discharge Resistance								
Discharge resistance	RDIS			150		Ω		

NOTES:

5) Guaranteed by over-temperature correlation, not tested in production.

6) Guaranteed by characterization, not tested in production.





2.5 3 3.5 4

4.5 5 5.5

INPUT VOLTAGE (V)

6

2.5 3 3.5 4 4.5

www.MonolithicPower.com MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited. 2017 MPS. All Rights Reserved.

INPUT VOLTAGE (V)

5

5.5 6



TYPICAL PERFORMANCE CHARACTERISTICS (continued)

VIN = EN = 5V, $T_A = 25^{\circ}C$, unless otherwise noted.



www.MonolithicPower.com

MPS Proprietary Information. Patent Protected. Unauthorized Photocopy and Duplication Prohibited. 2017 MPS. All Rights Reserved.



TYPICAL PERFORMANCE CHARACTERISTICS (continued)

VIN = EN = 5V, $T_A = 25^{\circ}C$, unless otherwise noted.





PIN FUNCTIONS

SOT563 Pin #	Name	Description
1, 6	NC	No connection.
2	VIN	Input power supply.
3	VOUT	Output to the load.
4	GND	Ground.
5	EN	Enable input. EN has an internal $1M\Omega$ pull-down resistor. Float EN to shut down the IC.



BLOCK DIAGRAM



Figure 1: Functional Block Diagram



OPERATION

The MP5075L is designed to limit the inrush current to the load when a circuit card is inserted into a live backplane power source, thereby limiting the backplane's voltage drop and the slew rate of the voltage to the load. The MP5075L provides an integrated solution to monitor the input voltage, output voltage, and output current to eliminate the need for an external current power MOSFET and current switch device.

Enable (EN)

When the input voltage is greater than the under-voltage lockout (UVLO) threshold (typically 2.6V), the MP5075L can be enabled by pulling EN above 1.5V. Pull EN down to ground to disable the MP5075L.

Current Limit

The MP5075L provides an internal, fixed, 1.4A, constant current limit. Once the device reaches its current limit threshold, the internal circuit regulates the gate voltage to hold the current in the power MOSFET constant. The typical response time is about 20µs. The output current may have a small overshoot during this time period.

If the current limit block starts to regulate the output current, the power loss on the power MOSFET causes the IC temperature to rise. If the junction temperature rises high enough, thermal shutdown is triggered. After thermal shutdown occurs, the output is disabled until the over-temperature fault is removed. The over-temperature threshold is 150°C, and hysteresis is 30°C.

Short-Circuit Protection (SCP)

If the load current increases rapidly due to a short circuit, the current may exceed the current limit threshold greatly before the control loop can respond. If the current reaches an internal secondary current limit level (typically 7A), a fast turn-off circuit activates to turn off the power MOSFET. This limits the peak current through the switch to limit the input voltage drop. The total short-circuit response time is about 200ns. If fast turn-off is effective, the power MOSFET remains off for 80µs. Afterward, the power MOSFET is turned on again. If the part is still in the short-circuit condition, the MP5075L enters current limit until the part is hot enough to trigger thermal shutdown. After the shortcircuit condition is removed, the MP5075L autoretries after the silicon temperature drops.

Output Discharge

The MP5075L has an output discharge function. This function can discharge VOUT by the internal pull-down resistance when the IC is disabled and the load is very light.

Soft Start (SS)

Soft start prevents large inrush current. The soft-start time is set to 450µs internally.

PCB Layout Guidelines

Efficient PCB layout is critical for stable operation. For best results, refer to Figure 2 and follow the guidelines below.

- 1. Place an input capacitor close to VIN.
- 2. Connect NC to GND for an easier layout.
- 3. Place enough vias around the IC and enough copper area near VIN and VOUT to achieve better thermal performance.



Figure 2: Recommended Layout



TYPICAL APPLICATION CIRCUIT





PACKAGE INFORMATION





TOP VIEW





FRONT VIEW



SIDE VIEW



NOTE:

SOT563

1) ALL DIMENSIONS ARE IN MILLIMETERS.

2) PACKAGE LENGTH DOES NOT INCLUDE MOLD FLASH, PROTRUSION OR GATE BURR.

3) PACKAGE WIDTH DOES NOT INCLUDE INTERLEAD FLASH OR PROTRUSION.

4) LEAD COPLANARITY (BOTTOM OF LEADS AFTER FORMING) SHALL BE 0.10 MILLIMETERS MAX.

5) DRAWING CONFORMS TO JEDEC MO-293, VARIATION UAAD. 6) DRAWING IS NOT TO SCALE.

RECOMMENDED LAND PATTERN

NOTICE: The information in this document is subject to change without notice. Please contact MPS for current specifications. Users should warrant and guarantee that third party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Monolithic Power Systems (MPS):

MP5075LGTF-P MP5075LGTF-Z