


### APPLICATIONS



- Battery-powered devices
- Embedded computing
- High-current SMPS
- High-frequency SMPS
- POL converters
- FPGA

### FEATURES

- Size 5.5mmx5.3mmx4.8mm
- Low DCR
- Low AC Losses
- Low Audible Noise
- Molded Construction
- Soft Saturation
- Stable Over High Temperatures
- Max Operating Temp +155°C
- RoHS/REACH-Compliant, Halogen-Free

### ELECTRICAL CHARACTERISTICS

| Parameter  |                  |      | Value | Unit |
|--|------------------|------|-------|------|
| Inductance <sup>(1)</sup>                          | $L$              | ±20% | 8.2   | μH   |
| Resistance   | $R_{DC}$         | typ  | 28    | mΩ   |
| Resistance <sub>MAX</sub>                          | $R_{DC\ MAX}$    | max  | 32.5  | mΩ   |
| Rated Current <sup>(2)</sup>                       | $I_R$            | typ  | 5.8   | A    |
| Saturation Current <sub>25°C</sub> <sup>(3)</sup>  | $I_{SAT\ 25°C}$  | typ  | 7.2   | A    |
| Saturation Current <sub>100°C</sub> <sup>(4)</sup> | $I_{SAT\ 100°C}$ | typ  | 7.2   | A    |
| Resonance Frequency                                | $f_r$            | typ  | 14    | MHz  |

### GENERAL SPECIFICATIONS

**(1) Inductance** Measured at 100kHz, 100mA

**(2) Rated Current**

Rated current will cause the coil temperature rise  $\Delta T$  of 40K  
 $I_R$  measured with the inductor soldered in a single-layer PCB. Copper layer thickness 35μm Cu / PCB size 30x50mm. Temperature behavior dependent on circuit design, PCB layout, proximity to other components, and trace dimensions and thickness.

**(3) Saturation Current <sub>25°C</sub>**

Saturation current will cause L to drop from 30% at 25°C ambient temperature

**(4) Saturation Current <sub>100°C</sub>**

Saturation current will cause L to drop from 30% at 100°C ambient temperature

**Temperature Test Condition**

Electrical specifications measured at 25°C, 35% RH if not given differently

**Operating Condition**


Operating temperature: -40°C to +155°C (including temp rise)  
 Should not exceed +155°C under worst-case operation conditions

**Storage Condition**


Tape and Reel packaging: -10°C to +40°C  
 Humidity: <50% RH

## TYPICAL PERFORMANCE CURVES


Temperature Rise vs. Current




Inductance vs. Current




Impedance vs. Frequency




Inductance vs. Frequency



**Quality Factor vs. Frequency**




**AC Resistance vs. Frequency**



## LAND PATTERN

### Dimensions


|   |                           |
|---|---------------------------|
| A | 4.70 ref.                 |
| B | 2.0 ref.                  |
| C | 4.50 ref.<br>(unit in mm) |



## PRODUCT PACKAGE AND DIMENSIONS

### Dimensions

(unit in mm)



## TOP MARKING

### Marking

|                  |         |
|------------------|---------|
| Start of Winding | · (dot) |
| Inductance Code  | 8R2     |
| MPS Code         | MPS     |

## ORDERING INFORMATION

| Part Number    | $L^{(1)}$ | $R_{DC}$ | $I_R^{(2)}$ | $I_{SAT\ 25^\circ C}^{(3)}$ | $I_{SAT\ 100^\circ C}^{(4)}$ |
|----------------|-----------|----------|-------------|-----------------------------|------------------------------|
|                | typ (μH)  | typ (mΩ) | typ (A)     | typ (A)                     | typ (A)                      |
| MPL-AL5050-5R6 | 5.6       | 20       | 6.8         | 8                           | 8                            |
| MPL-AL5050-6R8 | 6.8       | 25       | 6.1         | 7.6                         | 7.6                          |
| MPL-AL5050-8R2 | 8.2       | 28       | 5.8         | 7.2                         | 7.2                          |
| MPL-AL5050-100 | 10        | 37       | 4.8         | 5.5                         | 5.5                          |

## GENERAL SPECIFICATIONS

|   |  |
|---|--|
| <b>(1) Inductance</b>                                     | Measured at 100kHz, 100mA  |
| <b>(2) Rated Current</b>                                  | Rated current will cause the coil temperature rise $\Delta T$ of 40K<br><i><math>I_R</math> measured with the inductor soldered in a single-layer PCB. Copper layer thickness 35μm Cu / PCB size 30x50mm. Temperature behavior dependent on circuit design, PCB layout, proximity to other components, and trace dimensions and thickness.</i> |
| <b>(3) Saturation Current <math>_{25^\circ C}</math></b>  | Saturation current will cause L to drop from 30% at 25°C ambient temperature   |
| <b>(4) Saturation Current <math>_{100^\circ C}</math></b> | Saturation current will cause L to drop from 30% at 100°C ambient temperature  |
| <b>Temperature Test Condition</b>                         | Electrical specifications measured at 25°C, 35% RH if not given differently  |
| <b>Operating Condition</b>                                | Operating temperature: -40°C to +155°C (including temp rise)<br>Should not exceed +155°C under worst-case operation conditions   |
| <b>Storage Condition</b>                                  | Tape and Reel packaging: -10°C to +40°C<br>Humidity: <50% RH   |

**NOTICE:** The information in this document is subject to change without notice. Please contact MPS for current specifications. Users should warrant and guarantee that third-party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Monolithic Power Systems \(MPS\):](#)

[MPL-AL5050-8R2](#)