

RING TERMINAL SELECTION GUIDE



BU-190540044

BU-190540113



BU-191640063

BU-191930082

- Mueller offers a wide range of ring terminals that are suitable for a variety of applications.
- Three different wire ranges
 - 12-10AWG
 - 16-14AWG
 - 22-18AWG
- Stud sizes from #6 all the way up to 3/8"
- 4 different insulation styles
 - Nyax heat shrink
 - Nylon
 - Vinyl
 - Uninsulated-Brazed Seams
- Temperature ratings:
 - 75°C: Nylon and Vinyl insulated
 - 125°C: Nyax insulated
 - 175°C: Uninsulated
- Rated Voltage: 600V
- Single crimp terminals
- Solid or stranded wire accepted
- Recommended strip length: 1/4"
- All ring terminals are UL and CSE listed except the Nyax heat shrink insulated terminals
 - UL Listed, investigated to UL 486 A-B, File NO. ZMVB.E68376
 - CSA 22.2 No. 65-03, Certification NO. 207131

12-10AWG RING TERMINALS

PART NUMBER	AWG SIZE	STUD SIZE	INSULATION MATERIAL	BARREL LENGTH	LENGTH	W	STUD DIAMETER (SD)	F
BU-191640063	12-10	#10	NYAX HEAT SHRINK	.250	1.15	.342	.194/.197	.297
BU-191640066	12-10	1/4	NYAX HEAT SHRINK	.250	1.45	.558	.257/.261	.469
AI-50220N	12-10	#8	NYLON	.250	1.020	.342	.168/.171	.297
AI-50230N	12-10	#10	NYLON	.250	1.020	.342	.194/.197	.297
AI-50240N	12-10	1/4	NYLON	.250	1.30	.558	.257/.261	.469
AI-50250N	12-10	5/16	NYLON	.250	1.30	.558	.327/.323	.469
AI-50260N	12-10	3/8	NYLON	.250	1.30	.558	.400/.394	.469
BU-191930106	12-10	#8	UNINSULATED	.250	.720	.342	.168/.171	.297
BU-191930109	12-10	#10	UNINSULATED	.250	.720	.342	.194/.197	.297
BU-191930116	12-10	1/4	UNINSULATED	.250	.990	.558	.257/.261	.469
BU-191930120	12-10	5/16	UNINSULATED	.250	.990	.558	.327/.323	.469
BU-191930137	12-10	3/8	UNINSULATED	.250	.990	.558	.400/.394	.469
BU-190700121	12-10	#8	VINYL	.250	1.020	.342	.168/.171	.297
BU-190700123	12-10	#10	VINYL	.250	1.020	.342	.194/.197	.297
BU-190700132	12-10	1/4	VINYL	.250	1.30	.558	.257/.261	.469
BU-190700136	12-10	5/16	VINYL	.250	1.30	.558	.327/.323	.469
BU-190700153	12-10	3/8	VINYL	.250	1.30	.558	.400/.394	.469





MATERIAL:
110 COPPER ALLOY 0.038 THICK
ELECTRO-TIN PLATED .00025"-.0004"

*ALL DIMENSIONS ARE IN INCHES **CELL COLOR DEPICTS INSULATION COLOR

16-14AWG RING TERMINALS

PART NUMBER	AWG SIZE	STUD SIZE	INSULATION MATERIAL	BARREL LENGTH	LENGTH	W	STUD DIAMETER (SD)	F
BU-191640033	16-14	#8	NYAX HEAT SHRINK	.250	1.18	.324	.171/.168	.295
BU-191640034	16-14	#10	NYAX HEAT SHRINK	.250	1.18	.324	.197/.194	.295
BU-191640026	16-14	1/4	NYAX HEAT SHRINK	.250	1.40	.470	.265/.263	.405
AI-50086N	16-14	#6	NYLON	.188	.778	.295	.139/.142	.260
AI-50090N	16-14	#8	NYLON	.250	.930	.324	.168/.171	.295
AI-50100N	16-14	#10	NYLON	.250	.930	.324	.194/.197	.295
AI-50101N	16-14	1/4	NYLON	.250	1.110	.470	.263/.265	.405
AI-50102N	16-14	5/16	NYLON	.250	1.110	.470	.324/.327	.405
AI-50103N	16-14	3/8	NYLON	.250	1.210	.558	.394/.398	.569
BU-191930080	16-14	#8	UNINSULATED	.250	.710	.324	.168/.171	.295
BU-191930082	16-14	#10	UNINSULATED	.250	.710	.324	.194/.197	.295
BU-191930055	16-14	1/4	UNINSULATED	.250	.890	.470	.263/.265	.405
BU-191930074	16-14	5/16	UNINSULATED	.250	.890	.470	.324/.327	.405
BU-190540108	16-14	#6	VINYL	.250	.880	.295	.138/.142	.260
BU-190540110	16-14	#8	VINYL	.250	.930	.324	.168/.171	.295
BU-190540113	16-14	#10	VINYL	.250	.930	.324	.194/.197	.295
BU-190540086	16-14	1/4	VINYL	.250	1.110	.470	.263/.265	.405
BU-190540088	16-14	5/16	VINYL	.250	1.110	.470	.324/.327	.405
BU-190540075	16-14	3/8	VINYL	.250	1.210	.558	.394/.398	.569



MATERIAL:
110 COPPER ALLOY 0.03 THICK
ELECTRO-TIN PLATED .0001"-.0003"

*ALL DIMENSIONS ARE IN INCHES **CELL COLOR DEPICTS INSULATION COLOR



Mueller Electric Company
 2850 Gilchrist Rd. Bld 5A
 Akron, OH 44305

www.muellerelectric.com

Toll Free: 800.955.2629
 Phone: 330.780.2525
 Fax: 330.780.2524

22-18AWG RING TERMINALS

PART NUMBER	AWG SIZE	STUD SIZE	INSULATION MATERIAL	BARREL LENGTH	LENGTH	W	STUD DIAMETER (SD)	F
BU-191640085	22-18	#6	NYAX HEAT SHRINK	.250	1.18	.290	.142/.138	.260
BU-191640086	22-18	#8	NYAX HEAT SHRINK	.250	1.18	.324	.171/.168	.250
BU-191640003	22-18	#10	NYAX HEAT SHRINK	.250	1.18	.324	.197/.194	.250
AI-50020N	22-18	#6	NYLON	.250	.870	.290	.139/.142	.260
AI-50030N	22-18	#8	NYLON	.250	.880	.324	.168/.171	.250
AI-50040N	22-18	#10	NYLON	.250	.880	.324	.194/.197	.250
AI-50041N	22-18	1/4	NYLON	.250	1.110	.470	.260/.265	.405
AI-50042N	22-18	5/16	NYLON	.250	1.10	.470	.324/.327	.405
AI-50043N	22-18	3/8	NYLON	.250	1.20	.558	.394/.398	.469
BU-191930014	22-18	#8	UNINSULATED	.250	.660	.324	.168/.171	.250
BU-191930016	22-18	#10	UNINSULATED	.250	.660	.324	.194/.197	.250
BU-191930021	22-18	1/4	UNINSULATED	.250	.890	.470	.260/.265	.405
BU-191930023	22-18	5/16	UNINSULATED	.250	.860	.470	.324/.327	.405
BU-190540035	22-18	#6	VINYL	.250	.800	0.225	.122/.125	.223
BU-190540054	22-18	#8	VINYL	.250	.880	.324	.168/.171	.250
BU-190540039	22-18	#10	VINYL	.250	.880	.324	.194/.197	.250
BU-190540042	22-18	1/4	VINYL	.250	1.110	.470	.260/.265	.405
BU-190540044	22-18	5/16	VINYL	.250	1.10	.470	.324/.327	.405
BU-190540048	22-18	3/8	VINYL	.250	1.20	.558	.394/.398	.469



MATERIAL:

**110 COPPER ALLOY 0.028 THICK
ELECTRO-TIN PLATED .0001"-.0003"**

*ALL DIMENSIONS ARE IN INCHES **CELL COLOR DEPICTS INSULATION COLOR

Mueller Electric Company
2850 Gilchrist Rd. Bld 5A
Akron, OH 44305

www.muellerelectric.com

Toll Free: 800.955.2629
Phone: 330.780.2525
Fax: 330.780.2524

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mueller Electric:

[BU-191930137](#) [BU-190540075](#) [AI-50101N](#) [AI-50260N](#) [BU-190700136](#) [BU-191640085](#) [BU-190540110](#) [BU-191930074](#) [BU-190540044](#) [AI-50086N](#) [BU-190700153](#) [AI-50230N](#) [AI-50100N](#) [AI-50042N](#) [AI-50020N](#) [BU-191930080](#) [BU-190540113](#) [AI-50041N](#) [BU-191930021](#) [BU-190700121](#) [AI-50102N](#) [AI-50030N](#) [BU-191930109](#) [BU-191930016](#) [BU-191930082](#) [BU-191640086](#) [BU-191640003](#) [BU-190540042](#) [BU-190540039](#) [AI-50103N](#) [BU-191640033](#) [AI-50040N](#) [BU-191930120](#) [BU-191640063](#) [BU-190540108](#) [BU-190540086](#) [BU-191930116](#) [BU-190540048](#) [BU-190540088](#) [BU-190540054](#) [AI-50240N](#) [BU-191640026](#) [BU-191930023](#) [AI-50043N](#) [BU-190700123](#) [AI-50250N](#) [BU-190700132](#) [BU-191930055](#) [AI-50220N](#) [BU-191930106](#) [BU-191930014](#) [BU-191640066](#) [BU-190540035](#) [BU-191640034](#) [AI-50090N](#)