



SERIES**CM6149R
CM6149****Surface Mount
Low Profile CM Choke****SCHEMATIC**

Actual Size

Mechanical Configuration A flat top surface mount case with excellent coplanarity of terminals.

Physical Parameters

	Inches	Millimeters
A	0.212 ± 0.010	5.38 ± 0.25
B	0.285 ± 0.010	7.24 ± 0.25
C	0.060 ± 0.010	1.52 ± 0.25
D	0.250 ± 0.010	6.35 ± 0.25
E	0.200 ± 0.010	5.08 ± 0.25
F	0.025 ± 0.010	0.64 ± 0.25
G	0.40 (Ref. only)	1.02 (Ref. only)

Electrical Configuration

- 1) Inductance and DCR in table is for either L1 or L2.
- 2) Leakage Inductance tested at L1 with L2 shorted or at L2 with L1 shorted.
- 3) Windings balanced within 2%
- 4) Inductance tested @ 10 kHz

Operating Temperature Range -55°C to +105°C

Electrical Characteristics Measured at +25°C

Rated RMS Current Based upon 40°C temperaturerise from 25°C ambient.

Maximum Power Dissipation at 25°C 0.200 Watts

Inductance Tolerance Units are supplied to the tolerance indicated in the table.


Dielectric Withstanding Voltage 500 V RMS, 60Hz

DASH NUMBER*
L1 or L2 INDUCTANCE
+35% / -25% (μH)
DC RESISTANCE
MAXIMUM (OHMS)
RATED RMS CURRENT
(AMPS) MAXIMUM
LEAKAGE INDUCTANCE
TYPICAL (μH)

SERIES CM6149 FERRITE CORE

-253	25	0.010	3.0	0.20
-473	47	0.015	2.5	0.30
-683	68	0.020	2.0	0.40
-104	100	0.030	1.6	0.50
-154	150	0.040	1.3	0.70
-224	220	0.060	1.0	1.10
-334	330	0.090	0.75	1.50
-474	470	0.125	0.60	1.70
-684	680	0.170	0.50	2.00
-105	1000	0.250	0.40	2.80
-125	1200	0.350	0.30	3.50
-155	1500	0.500	0.24	4.30
-225	2200	0.750	0.18	6.00

*Complete part # must include series # PLUS the dash #

LAND PATTERN DIMENSIONS

Marking DELEVAN; CM6149, inductance with units. Note: An R after CM6149 indicates a RoHS component. A white dot indicates the location of pin 1.

Example: CM6149-154

DELEVAN

CM6149

150 uH

Packaging Tape & reel (16mm):

13" reel, 800 pieces max.; 7" reel not available

Bulk option available

Weight (Grams) 0.5 (Ref.)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

API Delevan:

[CM6149-253](#) [CM6149-473](#) [CM6149-683](#) [CM6149-104](#) [CM6149-154](#) [CM6149-224](#) [CM6149-334](#) [CM6149-474](#)
[CM6149-684](#) [CM6149-105](#) [CM6149-155](#) [CM6149-225](#) [CM6149R-253](#) [CM6149R-473](#) [CM6149R-683](#) [CM6149R-104](#)
[CM6149R-154](#) [CM6149R-224](#) [CM6149R-334](#) [CM6149R-474](#) [CM6149R-684](#) [CM6149R-105](#) [CM6149R-125](#)
[CM6149R-155](#) [CM6149R-225](#) [CM6149-125](#)