


# NCP03XH223F05RL



## Appearance & Shape



## Features

1. Excellent solderability and high stability in environment
2. Excellent long time aging stability
3. High accuracy in resistance and B-Constant
4. Reflow soldering possible
5. Lead is not contained in the product.
6. UL/cULcertified product.(UL1434, File No. E137188)

## Applications

|               |                                    |
|---------------|------------------------------------|
| Limited Usage | Consumer Grade(Mobile device etc.) |
|---------------|------------------------------------|

## Packaging Information

| Packaging | Specifications   | Standard Packing Quantity |
|-----------|------------------|---------------------------|
| RL        | 180mm Paper Tape | 15000                     |

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# NCP03XH223F05RL



## Specifications

|  |                |
|--|----------------|
| Resistance (25°C)                      | 22kΩ           |
| Resistance Value Tolerance (at 25°C)   | ±1%            |
| B-Constant (25/50°C)                   | 3380K          |
| B-Constant (25/50°C) Tolerance         | ±1%            |
| B-Constant(25/80°C) (Reference Value)  | 3428K          |
| B-Constant(25/85°C) (Reference Value)  | 3434K          |
| B-Constant(25/100°C) (Reference Value) | 3455K          |
| Max. Voltage                           | 5V             |
| Maximum Operating Current (25°C)       | 0.067mA        |
| Typical Dissipation Constant (25°C)    | 1mW/°C         |
| Operating Temperature Range            | -40°C to 125°C |
| Size Code (in mm)                      | 0.6x0.3mm      |
| Size Code (in inch)                    | 0.2x0.1inch    |
| Shape                                  | SMD            |
| Mass                                   | 0.00026g       |
| MSL                                    | 1              |

### Attention


1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.


Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# NCP03XH223F05RL

## Product Data



Resistance-Temperature Characteristics



Maximum Operating Voltage Reduction Characteristics

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Murata:

[NCP03XH223F05RL](#)