

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1719821142

Status:


Active

Overview:

Nano-Pitch I/O Interconnect System

Description:

Nano-Pitch I/O Receptacle, Right-Angle, Through Hole, without Cap, 42 Circuits



Series image - Reference only

Documents:	
3D Model	Application Specification AS-173162-0002-001 (PDF)
3D Model (PDF)	Packaging Specification PK-171982-9000-001 (PDF)
Drawing (PDF)	Packaging Specification PK-173307-0001-001 (PDF)
Product Specification PS-173162-0001-001 (PDF)	Symbol Footprint Data SYM-171982-1142-001 (PDF)
Application Specification AS-173162-0001-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	I/O Connectors
Series	171982
Application	Wire-to-Board
Component Type	Receptacle
Overview	Nano-Pitch I/O Interconnect System
Product Name	Nano-Pitch I/O
Type	N/A
UPC	889056600668
Physical	
Circuits (Loaded)	42
Circuits (maximum)	42
Color - Resin	Black
Durability (mating cycles max)	50
Gender	Receptacle
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.042/g
Number of Rows	2
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
Packaging Type	Embossed Tape on Reel
Panel Mount	No
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-40° to +80°C
Termination Interface: Style	Through Hole
Waterproof / Dustproof	No

Electrical

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

171982 Series

Current - Maximum per Contact	0.5A
Grounding to Panel	None
Shielded	No
Voltage - Maximum	30V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-173162-0001-001, AS-173162-0002-001
Electrical Model Document	EE-171982-0010-001
Packaging Specification	PK-171982-9000-001, PK-173307-0001-001
Product Specification	PS-173162-0001-001
S-Parameter Model	SP-171982-0010-001
Sales Drawing	SD-171982-1000-001
Symbol/Footprint Data	SYM-171982-1142-001

This document was generated on 10/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[171982-1142](#)