

# UHF RFID Tag Data sheet

## LXMS21NCMH-230

### Scope

This Data sheet, is applied to passive UHF tag.

-Specific applications: To give ID (identification) to consumer product, consumer equipment, industrial equipment and medical equipment (GHTF Class A and B) or its consumables for individual management by using radio waves.


-Unsuitable Application: Applications listed in “Limitation of applications” in this Data sheet.

### 1, General Descriptions

LXMS21NCMH-230 is an innovative RFID module which complies ISO/IEC 18000-63 / EPC Global Gen2v2.

This product can be used as an ultra small tag to be embedded into objects by glue or adhesive and so on.


This can be used globally with high performance and reliability.



#### **[Features]**

- Small and Robust package design
- UHF band (865~928MHz)
- ISO/IEC 18000-63 / EPC Global Gen2v2 Compliant
- Size is 2.0 x 1.25 x 0.55mm
- Using impinj M750
- Read range:13mm \*Reference
- RoHS compliant

### 2, Block Diagram



**All Rights Reserved, Copyright© Murata Manufacturing Co., Ltd.**


< Specification is subject to change without notice >

# UHF RFID Tag Data sheet

## LXMS21NCMH-230

### 3. Mechanical Information

[Dimension]



<Bottom View>



Unit:mm

| Mark | Dimensions |
|------|------------|
| L    | 2.00±0.20  |
| W    | 1.25±0.20  |
| T    | 0.55max.   |

### 4. Electrical characteristics

#### 4-1. Frequency range

865 – 928 MHz

#### 4-2. IC / Memory size

| Parameter           |                 | Description        | Remarks      |
|---------------------|-----------------|--------------------|--------------|
| IC                  |                 | Impinj M750        |              |
| Protocol            |                 | ISO/IEC 18000-63   |              |
|                     |                 | EPC global Gen2 V2 |              |
| Memory              | EPC             | Max 96 bit         | Read & Write |
|                     | TID             | 96 bit             | Read Only    |
|                     | Reserved memory | 32 bit Access      | Read & Write |
|                     |                 | 32 bit Kill        |              |
|                     | User            | 32 bit             |              |
| Data Retention Time |                 | ※10years           | Tamb = 22℃   |

※Reference value

All Rights Reserved, Copyright© Murata Manufacturing Co., Ltd.

< Specification is subject to change without notice >

# UHF RFID Tag Data sheet


## LXMS21NCMH-230

### **5. Reading range (reference only)**

Reading range varies by Output Power of Reader/Writer and an antenna.

**UHF band(865~928MHz): 13mm**

\*Measurement setup




### **6. Absolute maximum ratings**

| Symbol           | Parameter             | Min | Max | Unit |
|------------------|-----------------------|-----|-----|------|
| T <sub>stg</sub> | Storage temperature   | -40 | +85 | °C   |
| T <sub>amb</sub> | Operating temperature | -40 | +85 | °C   |

UHF RFID Tag Data sheet  
LXMS21NCMH-230

7. Packaging

7-1. Dimensions of tape




Unit: mm

| Symbol    | A        | B        | C       | D        | E        | F       |
|-----------|----------|----------|---------|----------|----------|---------|
| Dimension | 1.50±0.1 | 2.25±0.1 | 8.0±0.2 | 3.5±0.05 | 1.75±0.1 | 4.0±0.1 |

| Symbol    | G        | H       | J       | K         | t         |
|-----------|----------|---------|---------|-----------|-----------|
| Dimension | 2.0±0.05 | 4.0±0.1 | 1.5±0.1 | 0.60±0.05 | 0.25±0.05 |

7-2. Dimensions of reel




Unit: mm

| Symbol    | a         | b           | c         | d     | e      |
|-----------|-----------|-------------|-----------|-------|--------|
| Dimension | 2.0+/-0.5 | Φ13.0+/-0.2 | 9.0+/-0.3 | (Φ60) | (Φ180) |

# UHF RFID Tag Data sheet


## LXMS21NCMH-230

### 7-3. Packing (Moisture-proof package)



Reel will be packed in moisture-proof package together with desiccant and humidity indicator. After packing, the package will be heat-sealed.

### 7-4. Taping Diagrams




All Rights Reserved, Copyright© Murata Manufacturing Co., Ltd.

< Specification is subject to change without notice >

# UHF RFID Tag Data sheet

## LXMS21NCMH-230

### 7-5. Leader and Tail tape



Unit : mm

| Symbol | Item                   | Minimum length |
|--------|------------------------|----------------|
| A      | Tail                   | 160            |
| B      | Leader no components   | 100            |
| C      | Leader with cover tape | 400            |

### 7-6 Taping direction

The tape for chips are wound clockwise.

The feeding holes will come on the right side when the tape is pulled to a user's direction.

### 7-7. Quantity per reel

5,000 pcs

### 7-8. Minimum order quantity

5,000pcs

### 7-9. Material


Base and Cover tape : Plastic

Reel : Plastic

Base and Cover tape, Reel have an anti-ESD function.

### 7-10. Peeling force

0.1~1.0 N in the direction of peeling as shown below.



All Rights Reserved, Copyright© Murata Manufacturing Co., Ltd.

< Specification is subject to change without notice >

# UHF RFID Tag Data sheet

## LXMS21NCMH-230

### **8. Contact window**

URL: <http://www.murata.com/products/rfid>

Email: [magicstrap@murata.com](mailto:magicstrap@murata.com)

For any inquiries/queries, please feel free to contact us.

# UHF RFID Tag Data sheet

## LXMS21NCMH-230

### NOTICE

#### 1. Storage Conditions:

To avoid damaging, be sure to observe the following points.

- The product shall be stored without opening the packing under the ambient temperature from 5 to 35 deg.C and humidity from 20 to 70%RH.  
(Packing materials, in particular, may be deformed at the temperature over 40 deg.C.)
- The product left more than 6 months after reception, it needs to be baked before use.  
(Since adhesive tape, tape, and reel are not resistant to heat, baking with tape and reel is not possible. In case baking is necessary, please place the product into a heat resistant container. Baking condition should be 125deg.C, 24hours, once. )
- The product shall be stored in non corrosive gas (Cl<sub>2</sub>, NH<sub>3</sub>, SO<sub>2</sub>, NO<sub>x</sub>, etc.).
- Environment with high temperature or excessive temperature shift might cause dew condensation and deterioration of product performance.
- After the packing is opened, the product shall be stored at  $\leq 30$  deg.C /  $\leq 60$  %RH.
- When the color of the indicator in the packing changed, the product shall be baked before use.
- This product is applicable to MSL2 (Based on IPC/JEDEC J-STD-020)

#### 2. Handling Conditions:

Be careful in handling or transporting products because excessive stress or mechanical shock may break products.

Please see Appendix 1 for reference attachment condition in detail.

#### 3. Operational Environment Conditions:

Products are designed to work under normal environmental conditions (ambient temperature, humidity and pressure). Therefore, products have no problems to be used under the similar conditions to the above-mentioned. However, if products are used under the following circumstances, it may damage products and leakage of electricity and abnormal temperature may occur.

- In an atmosphere containing corrosive gas ( Cl<sub>2</sub>, NH<sub>3</sub>, SO<sub>x</sub>, NO<sub>x</sub> etc.).

**All Rights Reserved, Copyright© Murata Manufacturing Co., Ltd.**

< Specification is subject to change without notice >



# UHF RFID Tag Data sheet

## LXMS21NCMH-230

- In an atmosphere containing combustible and volatile gases.
- In a dusty environment.
- Direct sunlight
- Water splashing place.
- Humid place where water condenses.
- In a freezing environment.

If there are possibilities for products to be used under the preceding clause, consult with Murata before actual use.

If static electricity is added to this product, degradation and destruction may be produced.

Please use it after consideration enough so that neither static electricity nor excess voltage is added at the time of an assembly and measurement.

If product malfunctions may result in serious damage, including that to human life, alternative measures of the operation and design must be taken to secure the safety.

#### **4. Cleaning Conditions:**

If the cleaning will be applied, please check with Murata in advance since the product may degrade or get broken.

#### **5. Limitation of Applications:**

The products listed in the Data sheet (hereinafter the product(s) is called as the "Product(s)") are designed and manufactured for applications specified in the Data sheet. (hereinafter called as the "Specific Application").

We shall not warrant anything in connection with the Products including fitness, performance, adequateness, safety, or quality, in the case of applications listed in from (1) to (11) written at the end of this precautions, which may generally require high performance, function, quality, management of production or safety.

Therefore, the Product shall be applied in compliance with the specific application.

WE DISCLAIM ANY LOSS AND DAMAGES ARISING FROM OR IN CONNECTION WITH THE PRODUCTS INCLUDING BUT NOT LIMITED TO THE CASE SUCH LOSS AND DAMAGES CAUSED BY THE UNEXPECTED ACCIDENT, IN EVENT THAT (i) THE PRODUCT IS APPLIED FOR THE PURPOSE WHICH IS NOT SPECIFIED AS THE SPECIFIC APPLICATION FOR THE PRODUCT, AND/OR (ii) THE PRODUCT IS APPLIED FOR ANY FOLLOWING APPLICATION PURPOSES FROM (1) TO (11) (EXCEPT THAT SUCH APPLICATION PURPOSE IS UNAMBIGUOUSLY SPECIFIED AS SPECIFIC APPLICATION FOR THE PRODUCT IN OUR CATALOG SPECIFICATION FORMS, DATASHEETS, OR OTHER DOCUMENTS OFFICIALLY ISSUED BY US\*).

- (1) Aircraft equipment
- (2) Aerospace equipment
- (3) Undersea equipment
- (4) Power plant control equipment

**All Rights Reserved, Copyright© Murata Manufacturing Co., Ltd.**

< Specification is subject to change without notice >

# UHF RFID Tag Data sheet

## LXMS21NCMH-230

- (5) Medical equipment
- (6) Transportation equipment
- (7) Traffic control equipment
- (8) Disaster prevention/security equipment
- (9) Industrial data-processing equipment
- (10) Combustion/explosion control equipment
- (11) Equipment with complexity and/or required reliability equivalent to the applications listed in the above.

For exploring information of the Products which will be compatible with the particular purpose other than those specified in the Data sheet, please contact our sales offices, distribution agents, or trading companies with which you make a deal, or via our web contact form.

Contact form: <https://www.murata.com/contactform>

\*We may design and manufacture particular Products for applications listed in (1) to (11). Provided that, in such case we shall unambiguously specify such Specific Application in the Data sheet without any exception. Therefore, any other documents and/or performances, whether exist or non-exist, shall not be deemed as the evidence to imply that we accept the applications listed in (1) to (11).



### **Note:**

Please make sure that your product has been evaluated and confirmed against your specifications when our product is attached to your product.

All the items and parameters in this product specification have been prescribed on the premise that our product is used for the purpose, under the condition and in the environment agreed upon between you and us. You are requested not to use our product deviating from such agreement.

# UHF RFID Tag Data sheet

## LXMS21NCMH-230

### Appendix 1

#### < High temperature process >

Please make sure to avoid more than 2 times of heating process when this product is attached with high temperature process.

Temperature profile of the attaching process should not exceed below reflow mounting process.


Excessive heating process might damage this product.

The impact of heating process should be evaluated to confirm the reliability based on customers' use case.

Please consult with Murata in case heating process exceeds 217°C(solder paste melting point).

Reference: Reflow profile

#### Reflow profile



# UHF RFID Tag Data sheet

## LXMS21NCMH-230

### <Injection mold test>

Murata conducted the injection mold test, with the condition in table 1 and the result is shown in the table 2.  
This test is conducted with Murata test condition as a reference and not as a recommendation of attachment process.

Please make sure to conduct test with actual condition to confirm the reliability before use.

Table 1: Injection mold test

|                         |                        |
|-------------------------|------------------------|
| Plastic type            | PP                     |
| Plastic grade           | J106-GOS               |
| Mold temperature[°C]    | Upper mold : 40        |
|                         | Lower mold : 40        |
| Plastic temperature[°C] | Plastic material : 180 |
|                         | Nozzle : 200           |
| Injection time[Sec]     | 1.9                    |
| Chilling time[Sec]      | 15                     |
| First Pressure[MPa]     | 224                    |
| Holding Pressure[MPa]   | 224                    |

Table 2: Test result

| Item           | Specification                                | Test method | Qty | Result (NG) |
|----------------|--|-------------|-----|-------------|
| Injection mold | Satisfy specification listed in paragraph 5. | In Table 1  | 30  | 30 (0)      |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Murata:

[LXMS21NCMH-230](#)