Note: This datasheet may be out of date. Please download the latest datasheet of BLM21BB331SN1# from the official website of Murata Manufacturing

BLM21BB331SN1#

"#" indicates a package specification code.







< List of part numbers with package codes > BLM21BB331SN1D BLM21BB331SN1J BLM21BB331SN1B




Appearance & Shape



Packaging Information





Packaging	Specifications	Minimum Order Quantity
D	180mm Paper Tape	4000
J	330mm Paper Tape	10000
В	Bulk(Bag)	1000



Other Usage

For general

1 of 4

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.





Please download the latest datasheet of BLM21BB331SN1# from the official website of Murata Manufacturing Co., Ltd.

BLM21BB331SN1#

"#" indicates a package specification code.

Note: This datasheet may be out of date.



The chip ferrite beads BLM series is designed to work nearly as a resistor at noise frequencies, which greatly reduces the possibility of resonance and leaves signal wave forms undistorted. BLM series is effective in circuits without stable ground lines because BLM series does not need a connection to ground.

BLM_B series can minimize attenuation of the signal waveform due to its sharp impedance characteristics. Various impedances are available to match signal frequency.

The nickel barrier structure of the external electrodes provides excellent solder heat resistance.

2 of 4

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.



Note: This datasheet may be out of date. ${\bf Please\ download\ the\ latest\ data sheet\ of\ BLM21BB331SN1\#\ from\ the\ official\ website\ of\ Murata\ Manufacturing}$ Co., Ltd.

BLM21BB331SN1#

"#" indicates a package specification code.



Shape	SMD
Size Code (in mm)	2012
Size Code (in inch)	0805
Length	2.0mm
Length Tolerance	±0.2mm
Width	1.25mm
Width Tolerance	±0.2mm
Thickness	0.85mm
Thickness Tolerance	±0.2mm
Impedance (at 100MHz)	330Ω
Impedance (at 100MHz) Tolerance	±25%
Rated Current (at 85°C)	400mA
Rated Current (at 125°C)	400mA
DC Resistance(max.)	0.33Ω
Operating Temperature Range	-55°C to 125°C
Mass(typ.)	0.01g
Number of Circuit	1

3 of 4

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.







Note: This datasheet may be out of date Please download the latest datasheet of BLM21BB331SN1# from the official website of Murata Manufacturing Co., Ltd.

BLM21BB331SN1#

"#" indicates a package specification code.







Impedance-Frequency Characteristics

Equivalent Circuit

4 of 4

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Murata:

BLM21BB331SN1D BLM21BB331SN1B