

MHR0844SA506F70

In Production

RoHS

REACH



Packaging Information

Packaging	Specifications	Standard Packing Quantity
-	Bulk(Bag)	100

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

MHR0844SA506F70



Specifications

Power Rating	2.5W
Shape	Lead
Maximum Working Voltage	11.2kVdc
Resistance	50.0M Ω
Resistance Deviation	$\pm 1\%$
Single Use/Mold Use	Single use
Length	46.0mm
Height H	10.0mm
Lead Pitch P	40.64mm

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Murata:

[MHR0844SA506F70](#)