

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1726040003](#)
Status: **Active**
Overview: [T-Path 100-Gbps Connector Solutions](#)
Description: [T-Path 100-Gpbs Connector, Surface Mount, Right-Angle](#)

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family I/O Connectors
Series [172604](#)
Application Wire-to-Board
Comments Surface Mount Compatible - Immerse in molten solder at 245°C at a rate of 25.4mm per second. Solder Duration: 5 ± 0.5 seconds
Component Type Receptacle
Overview [T-Path 100-Gbps Connector Solutions](#)
Product Name T-Path
Type N/A
UPC 191128170246

Physical

Circuits (Loaded) 28
Circuits (maximum) 28
Color - Resin Black
Durability (mating cycles max) 250 (external interface), 30 (internal interface)
Flammability 94V-0
Keying to Mating Part None
Lock to Mating Part Yes
Material - Metal Copper Alloy
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin Liquid Crystal Polymer
Net Weight 2.547/g
Number of Rows 2
Orientation Right Angle
PCB Locator Yes
PCB Retention Yes
Packaging Type Embossed Tape on Reel
Panel Mount N/A
Pitch - Mating Interface 0.80mm
Plating min - Mating 0.762µm
Plating min - Termination 2.540µm
Polarized to Mating Part Yes
Polarized to PCB Yes
Surface Mount Compatible (SMC) Yes
Temperature Range - Operating -40° to +80°C
Termination Interface: Style Surface Mount

Electrical

Current - Maximum per Contact 1.0A
Grounding to Panel Yes



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ECHA_01_2020 (16
January 2020

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[172604](#) Series

Mates With

QSFP Cable Assembly [74757](#)
QSFP+ Cable Assembly [111040](#)
zQSFP+ Cable Assembly [100297](#) , [100345](#)

Voltage - Maximum	30V
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-172604-0003-001

This document was generated on 03/05/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[172604-0003](#)