



10		9		8		7	6	5	4	3	2	19270
BLACK		RED		MIN	MAX	RECOVERED	LENGTH					
MATERIAL NUMBER	ENGINEERING NUMBER	MATERIAL NUMBER	ENGINEERING NUMBER	EXPANDED ID "D"	RECOVERED ID	WALL THK REF	FEET/METERS					
192700008	PFB-04-1BK	192700013	PFB-04-1RD	.400/10.16	.150/3.81	.060/1.53	4.0/1.2					
192700018	PFB-07-1BK	192700023	PFB-07-1RD	.750/19.05	.220/5.59	.095/2.41						
192700028	PFB-11-1BK	192700033	PFB-11-1RD	1.100/27.94	.375/9.53	.120/3.05						
192700038	PFB-15-1BK	192700043	PFB-15-1RD	1.500/38.10	.500/19.05	.140/3.56						
192700048	PFB-20-1BK	192700053	PFB-20-1RD	2.000/50.380	.750/19.05	.155/3.98						
192700058	PFB-30-1BK	192700063	PFB-30-1RD	3.540/89.92	1.18/29.97	.155/3.98						
192700068	PFB-40-1BK	192700073	PFB-40-1RD	4.72/119.89	1.57/39.88	.170/4.37						



SALES DRAWING

NOTES:

- 1. MATERIAL: POLYOLEFIN
- 2. OTHER CUT LENGTHS ARE AVAILABLE.
- 3. PARTS ARE RoHS COMPLIANT.

(A1)

CHANGED TITLE EC NO: IFG2013-0982 DRAWN: GJOJAS01 2013/01/10 CHKD: JMACNEIL 2013/01/10 APPR: JMACNEIL 2013/01/31 A1	DESCRIPTION ▽=0 ▽=0	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 1:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY BENDERLE	DATE 2004/09/23	TITLE (A1) POLYOLEFIN HEAT SHRINK TUBING 19270 SERIES				
		4 PLACES	± ---	± ---	CHECKED BY	DATE						
		3 PLACES	± ---	± .010	R DEROSS	2004/09/23	MOLEX MOLEX INCORPORATED					
		2 PLACES	± 0.25	± .02	APPROVED BY	DATE						
		1 PLACE	± 0.51	± ---	R DEROSS	2004/09/23	DOCUMENT NO. SD-19270-001					
		ANGULAR ± ---°			MATERIAL NO.						SHEET NO. 1 OF 1	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE CHART							
					SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19270-0034](#)