



NOTE:

1. "XX" REFERS TO THE NUMBER OF CIRCUITS

2. DIM "A" FOR 11 CIRCUIT LENGTH TO 48
CIRCUIT LENGTH WILL HAVE A TOLERANCE
OF +/- .4 FOR 1 PLACE METRIC AND +/- .015
FOR 2 PLACE INCH.

MATERIAL NO. FLAT	MATERIAL NO. (ON EDGE (FORMED))	NUMBER OF CIRCUITS "XX"	DIM "A"	DIM "B"
387236602	387236502	02	17.1 [.68]	9.53 [.375]
387236603	380021284	03	26.7 (1.05)	19.05 (1.750)
387236604	380021286	04	36.2 (1.43)	28.58 (1.125)
	380021288	05	45.7 (1.80)	38.10 (1.500)
	387236506	06	55.2 (2.18)	47.63 (1.875)
	380021289	07	64.8 (2.55)	57.15 (2.250)
387236608	380021290	08	74.3 (2.93)	66.68 (2.625)
	380021291	09	83.8 (3.30)	76.20 (3.000)
	387236510	10	93.3 (3.68)	85.73 (3.375)
	387236511	11	102.9 (4.05)	95.25 (3.750)
	387236512	12	112.4 (4.43)	104.78 (4.125)
	387236513	13	121.9 (4.80)	114.30 (4.500)
	387236514	14	131.4 (5.18)	123.83 (4.875)
387236615	387236515	15	141.0 (5.55)	133.35 (5.250)
	387236516	16	150.5 (5.93)	142.88 (5.625)
		17	160.0 (6.30)	152.40 (6.000)
	387236518	18	169.5 (6.68)	161.93 (6.375)
		19	179.1 (7.05)	171.45 (6.750)
387236620	387236520	20	188.6 (7.43)	180.98 (7.125)
		21	198.1 (7.80)	190.50 (7.500)
	387236522	22	207.6 (8.18)	200.03 (7.875)
		23	217.2 (8.55)	209.55 (8.250)
	387236524	24	226.7 (8.93)	219.08 (8.625)
		25	236.2 (9.30)	228.60 (9.000)
		26	245.7 (9.68)	238.13 (9.375)
		27	255.3 (10.05)	247.65 (9.750)
		28	264.8 (10.43)	257.18 (10.125)
		29	274.3 (10.80)	266.70 (10.500)
387236630	387236530	30	283.8 (11.18)	276.23 (10.875)
		31	293.4 (11.55)	285.75 (11.250)
		32	302.9 (11.93)	295.28 (11.625)
		33	312.4 (12.30)	304.80 (12.000)
		34	321.9 (12.68)	314.33 (12.375)
		35	331.5 (13.05)	323.85 (12.750)
		36	341.0 (13.43)	333.38 (13.125)
		37	350.5 (13.80)	342.90 (13.500)
		38	360.0 (14.18)	352.43 (13.875)
		39	369.6 (14.55)	361.95 (14.250)
		40	379.1 (14.93)	371.48 (14.625)
		41	388.6 (15.30)	381.00 (15.000)
		42	398.1 (15.68)	390.53 (15.375)
		43	407.7 (16.05)	400.05 (15.750)
		44	417.2 (16.43)	409.58 (16.125)
		45	426.7 (16.80)	419.10 (16.500)
		46	436.2 (17.18)	428.63 (16.875)
		47	445.8 (17.55)	438.15 (17.250)
		48	455.3 (17.93)	447.68 (17.625)

1	XX	JUMPER, TERMINAL	BRASS	NICKEL PLATING
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

EC NO. RELEASED WH 7-30-03 CH'K: APPR.: A	DESCRIPTION MAJOR CRITICAL SPC S	GENERAL TOLERANCES: (UNLESS SPECIFIED)		SCALE 3:1	DESIGN UNITS <input type="checkbox"/> mm <input checked="" type="checkbox"/> INCH	THIRD ANGLE PROJECTION	PROJECT NO. -		-	-
							DIMENSIONS:		SHT	REV
							<input checked="" type="checkbox"/> mm <input type="checkbox"/> INCH	<input type="checkbox"/> mm ONLY	REVISE ON CAD ONLY	
		4 PLACES ±.0015		DRAWN BY & DATE W. HOWARD 7-30-03		TITLE: JUMPER, TERMINAL				
		3 PLACES ±.038 ±.005		CHECKED BY & DATE						
		2 PLACES ±.13 ±.01		APPROVED BY & DATE						
		1 PLACE ±.3								
		ANGULAR: ±1°		CAD FILENAME 720435		MATERIAL NO. SEE CHART		DRAWING NO. SD-38002-002		SHEET NO. 1 OF 1
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.						
						SIZE B				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

38002-1290