






10			9			8	
NO. OF CIRCUITS	DIM. "A" mm in		DIM. "B" mm in		ASSEMBLY MATERIAL NO. (STANDARD)	ASSEMBLY MATERIAL NO. (-50 OPT)	
02	17.9	.71	8.3	.33	386906602	386907802	
03	26.2	1.03	16.5	.65	386906603	386907803	
04	34.4	1.36	24.8	.98	386906604	386907804	
05	42.7	1.68	33.0	1.30	386906605	386907805	
06	50.9	2.01	41.3	1.63	386906606	386907806	
07	59.2	2.33	49.5	1.95	386906607	386907807	
08	67.4	2.66	57.8	2.28	386906608	386907808	
09	75.7	2.98	66.0	2.60	386906609	386907809	
10	83.9	3.31	74.3	2.93	386906610	386907810	
11	92.2	3.63	82.6	3.25	386906611	386907811	
12	100.5	3.96	90.8	3.58	386906612	386907812	
13	108.7	4.28	99.1	3.90	386906613	386907813	
14	117.0	4.61	107.3	4.23	386906614	386907814	
15	125.2	4.93	115.6	4.55	386906615	386907815	
16	133.5	5.26	123.8	4.88	386906616	386907816	
17	141.7	5.58	132.1	5.20	386906617	386907817	
18	150.0	5.91	140.3	5.53	386906618	386907818	
19	158.2	6.23	148.6	5.85	386906619	386907819	
20	166.5	6.56	156.8	6.18	386906620	386907820	
21	174.8	6.88	165.1	6.50	386906621	386907821	
22	183.0	7.21	173.4	6.83	386906622	386907822	
23	191.3	7.53	181.6	7.15	386906623	386907823	
24	199.5	7.86	189.9	7.48	386906624	386907824	
25	207.8	8.18	198.1	7.80	386906625	386907825	
26	216.0	8.51	206.4	8.13	386906626	386907826	
27	224.3	8.83	214.6	8.45	386906627	386907827	
28	232.5	9.16	222.9	8.78	386906628	386907828	
29	240.8	9.48	231.1	9.10	386906629	386907829	
30	249.0	9.81	239.4	9.43	386906630	386907830	
31	257.3	10.13	247.7	9.75	386906631	386907831	
32	265.6	10.46	255.9	10.08	386906632	386907832	



NOTES:
1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE.
3. "XX" REFERS TO THE QUANTITY OF CIRCUITS.
4. ROHS COMPLIANT.

4	XX	SCREW #6-32X.155 PAN PHLZN/BR/STEEL -50 OPT	STEEL	ZN, CLEAR CHROMATE
3	XX	SCREW #6-32X.160 PAN PHLNI/BRASS (STANDARD)	BRASS	NICKEL PLATE
2	XX	TERMINAL, PC	BRASS	TIN PLATE
1	1	INSULATOR	POLYESTER (PBT)	BLACK
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

REV	DESCRIPTION
2012/06/01	APPR: JMACNEIL
2012/05/31	CHK'D: JMACNEIL
2012/05/22	DRWN: JENCINAS
2012/05/22	EC NO: IPG2012-0967
REMOVE "USA"	

QUALITY SYMBOLS

 = 0

 = 0

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	± .---	± ---
3 PLACES	± .---	± .005
2 PLACES	± 0.13	± .01
1 PLACE	± 0.3	± ---
ANGULAR ± 2 °		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE	
MM/IN	
DRAWN BY	DATE
AHIDALGO	2007/04/02
CHECKED BY	DATE
JENCINAS	2007/04/02
APPROVED BY	DATE
JMACNEIL	2012/06/0
MATERIAL NO.	
SEE CHART	
SIZE B	THIS DRAWING CONTAINS INCORPORATED AND

SCALE 2:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION
TITLE 8.26/.325 SR TRI-BARRIER TERMINAL STRIP CS, PC ASSY		
 MOLEX INCORPORATED		
DOCUMENT NO. SD-38690-001		SHEET NO. 1 OF 1
THIS INFORMATION THAT IS PROPRIETARY TO MOLEX SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[38690-7823](#) [38690-7824](#) [38690-7815](#) [38690-7813](#) [38690-7814](#) [38690-7802](#) [38690-7816](#) [38690-7817](#) [38690-7818](#) [38690-7819](#) [38690-7820](#) [38690-7821](#) [38690-7822](#) [38690-7825](#) [38690-7826](#) [38690-7827](#) [38690-7828](#) [38690-7829](#) [38690-7830](#)