

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200868659](#)  
**Status:** **Active**  
**Overview:** Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable  
**Description:** Nano-Change (M8) Single-Ended Cordset with Knurled Hexnut, 4 Poles, Female (Straight) to Pigtail, 24 AWG, WSOR Cable, 1.0m (3.28') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                    |  |
|--------------------|--|
| Product Family     | Industrial Cordsets  |
| Series             | <a href="#">120086</a>   |
| Connector End A    | Nano-Change (M8)   |
| Connector End B    | Pigtail  |
| IP Rating          | IP67   |
| Material - Contact | Brass  |
| Overview           | <a href="#">Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable</a> |
| Product Name       | Nano-Change (M8)   |
| Protocol           | N/A  |
| Region             | Europe   |
| Type               | Single Ended   |
| UPC                | 889056003643   |

**Physical**

|                               |                          |
|-------------------------------|--------------------------|
| Cable Diameter                | 4.80mm (.189")           |
| Cable Length                  | 1.0m (3.28')             |
| Color - Cable Jacket          | Black                    |
| Coupling Style                | Knurled Hexnut, Threaded |
| Gender                        | Female-Pigtail           |
| Keyway                        | A-coded                  |
| LED Indicator                 | No                       |
| Material - Cable Jacket       | TPU                      |
| Material - Connector Body     | TPU                      |
| Material - Coupling Nut       | Nickel-plated Brass      |
| Material - O-Ring             | Fluoro-elastomer         |
| Material - Plating Mating     | Gold                     |
| Net Weight                    | 1245.000/g               |
| Orientation                   | Straight to Pigtail      |
| Poles                         | 4                        |
| Temperature Range - Operating | -25°C to +85°C           |
| Wire Size AWG                 | 24                       |
| Wire/Cable Type               | UL 21215                 |

**Electrical**

|                               |                 |
|-------------------------------|-----------------|
| Current - Maximum per Contact | 3.0A            |
| Voltage - Maximum             | 60V AC / 75V DC |

**Material Info**

|                    |               |
|--------------------|---------------|
| Engineering Number | 404000B41M010 |
|--------------------|---------------|

**Reference - Drawing Numbers**

|               |                |
|---------------|----------------|
| Sales Drawing | 1200868655-00P |
|---------------|----------------|



*Series image - Reference only*

**EU ELV**

**Compliant with Exemption 3**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - D(2020)9139-DC (19 Jan 2021)

Lead

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Not Relevant

Compliant with

Exemption 3

Not Contained

**Search Parts in this Series**

[120086 Series](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1200868659](#)