

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200878409

Status:

Active

Overview:

Brad Nano-Change (M8) Products

Description:

Nano-Change (M8) to Micro-Change (M12) Double-Ended Cordset, 3 Poles, Female (Straight) to Male (Straight), 0.25mm² PVC Cable, 5.0m (16.40') Length

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E152210
General	
Product Family	Industrial Cordsets
Series	120087
Connector End A	Nano-Change (M8)
Connector End B	Micro-Change (M12)
IP Rating	IP68
Material - Contact	Copper Alloy
Overview	Brad Nano-Change (M8) Products
Product Name	Micro-Change (M12), Nano-Change (M8)
Protocol	N/A
Region	Europe
Type	Double Ended
UPC	78172532367
Physical	
Cable Diameter	N/A
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Female-Male
Keyway	None
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	199.677/g
Orientation	Straight to Straight
Poles	3
Temperature Range - Operating	-30°C TO +80°C
Wire Size AWG	N/A
Wire/Cable Type	UL 2464
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC / 75V DC
Material Info	
Engineering Number	483030E02M050

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)9139-DC (19 Jan 2021)

Lead

Halogen-Free Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

120087 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

120087-8409