



NL4MDXX-V-2

This connector is fully compliant to the device standard IEC 62368-1, due to its component certification according to IEC 61984.

4 pole chassis connector, black D-size flange, mirrored self tapping screw holes (A-screw), vertical PCB mount.

The speakON panel mount connectors are the standard chassis connectors for loudspeaker / amplifier interconnections. They feature a unique metal locking system, making contact only once fully locked. The speakON receptacles are robust, versatile and easy to terminate.

Features & Benefits

- IEC 61984 certified > IEC 62368-1 compliant
- Precise keyway for secure mating
- Metal insert in locking area
- Glass reinforced V-0 materials make it extremely robust and dependable
- Accurate twist lock latching system
- Airtight design - optimized for speaker applications

Technical Information

Product	
Title	NL4MDXX-V-2
Gender	male

Electrical	
Contact resistance	≤ 2 mΩ
Dielectric strength	4 kVdc (peak)
Insulation resistance	> 1 GΩ (after dampheat)
Rated current per contact	25 A rms continuous (audio rating significantly higher, depending on signal)

Mechanical	
Lifetime	> 5000 mating cycles
Wiring	vertical PCB mount
Locking device	Quick Lock
Mounting direction	Rear mounting
Chassis shape	D
Layout	Mirrored hole position, self tapping screw holes (A-Screw)

Material	
Contact plating	Ag
Locking element	Stainless Steel
Shell	Polyamide (PA 6.6)
Contacts	Copper Alloy

Environmental	
Flammability	UL 94 V-0
Temperature range	-30 °C to +80 °C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Neutrik:

[NL4MDXXV2](#) [NL4MDXX-V-2](#)